

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494093

Luminaire Tested: **LDA2B059727R60D010 2LBD1WMH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059727R60D010 2LBD1WMH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 533.9 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494093

CATALOG NUMBER: LDA2B059727R60D010 2LBD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P494093

CATALOG NUMBER: LDA2B059727R60D010 2LBD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319649
5°	303437
10°	297077
15°	287510
20°	262880
25°	233423
30°	174608
35°	98594
40°	37097
45°	16606
50°	8059
55°	1634
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P494093

CATALOG NUMBER: LDA2B059727R60D010 2LBD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	10.9
10°-20°	156.3	29.3
20°-30°	191.0	35.8
30°-40°	104.2	19.5
40°-50°	20.8	3.9
50°-60°	3.0	0.6
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.4	75.9
0°-40°	509.6	95.4
0°-60°	533.4	99.9
0°-90°	533.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	613	58
15°	563	156
25°	429	191
35°	164	104
45°	24	21
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494093

CATALOG NUMBER: LDA2B059727R60D010 2LBD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	647.9
1°	644.9
2°	639.2
3°	631.6
4°	620.8
5°	612.7
6°	608.4
7°	603.2
8°	599.2
9°	597.3
10°	593.0
11°	588.1
12°	583.8
13°	578.6
14°	571.0
15°	562.9
16°	552.6
17°	538.3
18°	529.1
19°	514.2
20°	500.7
21°	488.3
22.5°	467.4
23°	458.8
24°	445.5
25°	428.8
26°	407.4
27°	384.9
28°	359.2
29°	334.9
30°	306.5
32.5°	235.1
35°	163.7
37.5°	102.5
40°	57.6
42.5°	36.0
45°	23.8
47.5°	16.2
50°	10.5
52.5°	5.4
55°	1.9
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3



TEST NUMBER: P494093

CATALOG NUMBER: LDA2B059727R60D010 2LBD1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)