

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P491949

Luminaire Tested: **LDA2B058030R65D010 2LBD1H**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P491949
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058030R65D010 2LBD1H
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 787.4 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P491949
CATALOG NUMBER: LDA2B058030R65D010 2LBD1H

Luminous Intensity Polar Plot





TEST NUMBER: P491949

CATALOG NUMBER: LDA2B058030R65D010 2LBD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	427794
5°	393424
10°	375980
15°	361060
20°	332551
25°	308001
30°	282222
35°	207246
40°	98151
45°	32304
50°	10438
55°	1376
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P491949

CATALOG NUMBER: LDA2B058030R65D010 2LBD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	9.5
10°-20°	196.6	25.0
20°-30°	260.8	33.1
30°-40°	206.3	26.2
40°-50°	45.1	5.7
50°-60°	3.4	0.4
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.0	67.6
0°-40°	738.3	93.8
0°-60°	786.8	99.9
0°-90°	787.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	867	
5°	794	75
15°	707	197
25°	566	261
35°	344	206
45°	46	45
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P491949

CATALOG NUMBER: LDA2B058030R65D010 2LBD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	867.1
1°	862.5
2°	846.5
3°	829.0
4°	810.8
5°	794.4
6°	783.9
7°	773.4
8°	766.4
9°	755.9
10°	750.5
11°	741.9
12°	732.2
13°	723.7
14°	713.9
15°	706.9
16°	689.1
17°	680.1
18°	665.3
19°	651.7
20°	633.4
21°	618.7
22.5°	599.2
23°	593.8
24°	579.0
25°	565.8
26°	557.6
27°	544.0
28°	530.8
29°	514.8
30°	495.4
32.5°	427.7
35°	344.1
37.5°	245.4
40°	152.4
42.5°	85.9
45°	46.3
47.5°	24.9
50°	13.6
52.5°	5.8
55°	1.6
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4



TEST NUMBER: P491949

CATALOG NUMBER: LDA2B058030R65D010 2LBD1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)