

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494113

Luminaire Tested: **LDA2B059727R65D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494113  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059727R65D010 2LBD1MW  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 547.8 lumens  
Efficiency: N/A  
Efficacy: 78.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494113

CATALOG NUMBER: LDA2B059727R65D010 2LBD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P494113

CATALOG NUMBER: LDA2B059727R65D010 2LBD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	297596
5°	273673
10°	261558
15°	251195
20°	231378
25°	214262
30°	196313
35°	144187
40°	68268
45°	22467
50°	7292
55°	946
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P494113

CATALOG NUMBER: LDA2B059727R65D010 2LBD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.9	9.5
10°-20°	136.8	25.0
20°-30°	181.4	33.1
30°-40°	143.5	26.2
40°-50°	31.4	5.7
50°-60°	2.3	0.4
60°-70°	0.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.1	67.6
0°-40°	513.6	93.8
0°-60°	547.3	99.9
0°-90°	547.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	547.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	603	
5°	553	52
15°	492	137
25°	394	181
35°	239	144
45°	32	31
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494113

CATALOG NUMBER: LDA2B059727R65D010 2LBD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	603.2
1°	600.0
2°	588.9
3°	576.7
4°	564.0
5°	552.6
6°	545.3
7°	538.0
8°	533.2
9°	525.9
10°	522.1
11°	516.1
12°	509.4
13°	503.4
14°	496.6
15°	491.8
16°	479.3
17°	473.1
18°	462.8
19°	453.4
20°	440.7
21°	430.4
22.5°	416.9
23°	413.1
24°	402.8
25°	393.6
26°	387.9
27°	378.4
28°	369.2
29°	358.2
30°	344.6
32.5°	297.6
35°	239.4
37.5°	170.7
40°	106.0
42.5°	59.8
45°	32.2
47.5°	17.3
50°	9.5
52.5°	4.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.3
65°	0.3



TEST NUMBER: P494113

CATALOG NUMBER: LDA2B059727R65D010 2LBD1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)