

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279237

Luminaire Tested: **LDA2B058035D010 EU2B05FL408035 2LBAD1B**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279237  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B058035D010 EU2B05FL408035 2LBAD1B  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, B  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 853.9 lumens  
Efficiency: N/A  
Efficacy: 122.0 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279237

CATALOG NUMBER: LDA2B058035D010 EU2B05FL408035 2LBAD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P279237

CATALOG NUMBER: LDA2B058035D010 EU2B05FL408035 2LBAD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																												
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1174102
5°	1149269
10°	1047484
15°	818298
20°	484493
25°	180076
30°	56285
35°	25055
40°	11593
45°	5442
50°	2993
55°	1720
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P279237

CATALOG NUMBER: LDA2B058035D010 EU2B05FL408035 2LBAD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	214.5	25.1
10°-20°	426.6	50.0
20°-30°	174.7	20.5
30°-40°	28.9	3.4
40°-50°	6.8	0.8
50°-60°	1.8	0.2
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	815.8	95.5
0°-40°	844.7	98.9
0°-60°	853.4	99.9
0°-90°	853.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	853.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2380	
5°	2321	215
15°	1602	427
25°	331	175
35°	42	29
45°	8	7
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279237

CATALOG NUMBER: LDA2B058035D010 EU2B05FL408035 2LBAD1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2379.8
1°	2371.6
2°	2360.6
3°	2350.8
4°	2337.8
5°	2320.6
6°	2295.1
7°	2261.8
8°	2214.4
9°	2156.7
10°	2090.9
11°	2014.5
12°	1928.2
13°	1829.8
14°	1720.5
15°	1602.1
17.5°	1270.4
20°	922.8
22.5°	590.7
25°	330.8
27.5°	174.4
30°	98.8
32.5°	62.7
35°	41.6
37.5°	27.4
40°	18.0
42.5°	11.8
45°	7.8
47.5°	5.5
50°	3.9
52.5°	2.7
55°	2.0
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279237

CATALOG NUMBER: LDA2B058035D010 EU2B05FL408035 2LBAD1B

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)