

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494149

Luminaire Tested: **LDA2B059727R70D010 2LBDL1WMH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059727R70D010 2LBDL1WMH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 491.2 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494149

CATALOG NUMBER: LDA2B059727R70D010 2LBDL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P494149

CATALOG NUMBER: LDA2B059727R70D010 2LBDL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194434
5°	193295
10°	192023
15°	188473
20°	181659
25°	173924
30°	165664
35°	136718
40°	88877
45°	46398
50°	21568
55°	7913
60°	789
65°	584
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P494149

CATALOG NUMBER: LDA2B059727R70D010 2LBDL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	7.5
10°-20°	103.7	21.1
20°-30°	147.2	30.0
30°-40°	137.6	28.0
40°-50°	55.3	11.3
50°-60°	9.7	2.0
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	287.8	58.6
0°-40°	425.4	86.6
0°-60°	490.4	99.9
0°-90°	491.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	491.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	394	
5°	390	37
15°	369	104
25°	320	147
35°	227	138
45°	66	55
55°	9	10
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494149

CATALOG NUMBER: LDA2B059727R70D010 2LBDL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	394.1
1°	394.7
2°	393.9
3°	392.2
4°	391.4
5°	390.3
6°	386.0
7°	387.4
8°	383.6
9°	382.8
10°	383.3
11°	379.8
12°	379.0
13°	374.7
14°	373.0
15°	369.0
16°	366.5
17°	361.7
18°	356.0
19°	352.7
20°	346.0
21°	340.8
22.5°	331.4
23°	328.9
24°	324.3
25°	319.5
26°	315.7
27°	310.3
28°	304.9
29°	298.4
30°	290.8
32.5°	264.3
35°	227.0
37.5°	182.9
40°	138.0
42.5°	98.5
45°	66.5
47.5°	43.8
50°	28.1
52.5°	17.6
55°	9.2
57.5°	3.0
60°	0.8
62.5°	0.5
65°	0.5



TEST NUMBER: P494149

CATALOG NUMBER: LDA2B059727R70D010 2LBDL1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)