

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492020

Luminaire Tested: **LDA2B058035R20D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492020
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058035R20D010 2LBDL1GPH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 755.5 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492020
CATALOG NUMBER: LDA2B058035R20D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P492020

CATALOG NUMBER: LDA2B058035R20D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	98	97	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92	92	92	92
4	106	101	98	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90	90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88	88	88	88
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	86	86	86	86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84	84	84	84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82	82	82	82
9	94	88	85	82	93	88	84	82	87	84	82	86	84	82	86	83	81	81	81	81	81
10	92	86	83	80	91	86	83	80	85	82	80	85	82	80	84	82	80	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2497447
5°	2110938
10°	1286197
15°	529153
20°	190531
25°	76429
30°	34694
35°	16322
40°	8630
45°	4675
50°	2686
55°	1376
60°	789
65°	467
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P492020

CATALOG NUMBER: LDA2B058035R20D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.6	46.5
10°-20°	304.1	40.3
20°-30°	73.3	9.7
30°-40°	18.8	2.5
40°-50°	5.6	0.7
50°-60°	1.6	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.0	96.5
0°-40°	747.8	99.0
0°-60°	755.1	99.9
0°-90°	755.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5062	
5°	4262	352
15°	1036	304
25°	140	73
35°	27	19
45°	7	6
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492020

CATALOG NUMBER: LDA2B058035R20D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5062.1
1°	5018.0
2°	4913.0
3°	4753.4
4°	4547.8
5°	4262.4
6°	3967.5
7°	3641.9
8°	3303.8
9°	2924.4
10°	2567.4
11°	2194.3
12°	1867.2
13°	1557.7
14°	1273.9
15°	1036.0
16°	839.4
17°	677.8
18°	546.9
19°	449.8
20°	362.9
22.5°	223.7
25°	140.4
27.5°	91.2
30°	60.9
32.5°	40.1
35°	27.1
37.5°	18.9
40°	13.4
42.5°	9.4
45°	6.7
47.5°	5.1
50°	3.5
52.5°	2.4
55°	1.6
57.5°	1.2
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P492020

CATALOG NUMBER: LDA2B058035R20D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)