

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494193

Luminaire Tested: **LDA2B059730R20D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059730R20D010 2LBDLC1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 590.4 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.34
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494193

CATALOG NUMBER: LDA2B059730R20D010 2LBDLC1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P494193

CATALOG NUMBER: LDA2B059730R20D010 2LBDLC1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	105	104	103	102	102	100	100	99	99	97	97	97	97
2	112	109	106	104	110	107	105	102	104	102	100	100	101	100	98	98	98	97	96	96	95	95	95	95
3	109	105	101	99	107	103	100	98	101	98	96	96	99	97	95	95	97	95	94	94	92	92	92	92
4	106	101	98	95	104	100	97	94	98	95	93	93	96	94	92	92	95	93	91	91	90	90	90	90
5	103	98	94	92	102	97	94	91	96	93	90	90	94	92	90	90	93	91	89	89	88	88	88	88
6	101	95	91	89	100	95	91	88	93	90	88	88	92	89	87	87	91	89	87	87	86	86	86	86
7	98	93	89	86	97	92	89	86	91	88	86	86	90	87	85	85	89	87	85	85	84	84	84	84
8	96	90	87	84	95	90	86	84	89	86	84	84	88	85	83	83	87	85	83	83	82	82	82	82
9	94	88	85	82	93	88	84	82	87	84	82	82	86	84	82	82	86	83	81	81	81	81	81	81
10	92	86	83	80	91	86	83	80	85	82	80	80	85	82	80	80	84	82	80	80	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1951937
5°	1649864
10°	1005252
15°	413567
20°	148897
25°	59717
30°	27117
35°	12768
40°	6698
45°	3628
50°	2149
55°	1032
60°	592
65°	350
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494193

CATALOG NUMBER: LDA2B059730R20D010 2LBDLC1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.8	46.5
10°-20°	237.7	40.3
20°-30°	57.3	9.7
30°-40°	14.7	2.5
40°-50°	4.4	0.7
50°-60°	1.2	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.8	96.5
0°-40°	584.5	99.0
0°-60°	590.1	99.9
0°-90°	590.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	590.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3956	
5°	3331	275
15°	810	238
25°	110	57
35°	21	15
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494193

CATALOG NUMBER: LDA2B059730R20D010 2LBDLC1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3956.4
1°	3922.0
2°	3840.0
3°	3715.2
4°	3554.5
5°	3331.4
6°	3100.9
7°	2846.5
8°	2582.2
9°	2285.7
10°	2006.6
11°	1715.0
12°	1459.3
13°	1217.5
14°	995.6
15°	809.7
16°	656.1
17°	529.8
18°	427.4
19°	351.5
20°	283.6
22.5°	174.9
25°	109.7
27.5°	71.3
30°	47.6
32.5°	31.3
35°	21.2
37.5°	14.8
40°	10.4
42.5°	7.4
45°	5.2
47.5°	4.0
50°	2.8
52.5°	1.8
55°	1.2
57.5°	0.9
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P494193

CATALOG NUMBER: LDA2B059730R20D010 2LBDLC1MMS

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)