

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494358

Luminaire Tested: **LDA2B059730R70D010 2LBDL1H**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059730R70D010 2LBDL1H
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 522.7 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494358
CATALOG NUMBER: LDA2B059730R70D010 2LBDL1H

Luminous Intensity Polar Plot





TEST NUMBER: P494358

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206965
5°	205725
10°	204397
15°	200578
20°	193314
25°	185084
30°	176318
35°	145451
40°	94545
45°	49399
50°	22949
55°	8429
60°	888
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P494358

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	7.5
10°-20°	110.4	21.1
20°-30°	156.6	30.0
30°-40°	146.5	28.0
40°-50°	58.9	11.3
50°-60°	10.3	2.0
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.3	58.6
0°-40°	452.7	86.6
0°-60°	521.9	99.8
0°-90°	522.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	522.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	415	39
15°	393	110
25°	340	157
35°	242	146
45°	71	59
55°	10	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494358

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	419.5
1°	420.0
2°	419.2
3°	417.5
4°	416.6
5°	415.4
6°	410.8
7°	412.3
8°	408.2
9°	407.4
10°	408.0
11°	404.2
12°	403.3
13°	398.7
14°	397.0
15°	392.7
16°	390.1
17°	384.9
18°	378.9
19°	375.4
20°	368.2
21°	362.8
22.5°	352.7
23°	350.1
24°	345.2
25°	340.0
26°	336.0
27°	330.2
28°	324.5
29°	317.6
30°	309.5
32.5°	281.3
35°	241.5
37.5°	194.6
40°	146.8
42.5°	104.8
45°	70.8
47.5°	46.6
50°	29.9
52.5°	18.7
55°	9.8
57.5°	3.2
60°	0.9
62.5°	0.6
65°	0.6



TEST NUMBER: P494358

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)