

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492246

Luminaire Tested: **LDA2B058040R20D010 2LBDLC1MB-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058040R20D010 2LBDLC1MB-30DEG TILT
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 533.8 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492246

CATALOG NUMBER: LDA2B058040R20D010 2LBDLC1MB-30DEG TILT

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P492246

CATALOG NUMBER: LDA2B058040R20D010 2LBDLC1MB-30DEG TILT

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	8486	8486	8486
5°	16195	7478	5448
10°	38725	6563	3707
15°	225758	5210	1481
20°	1126125	3203	420
25°	2053397	1089	0
30°	2408401	0	0
35°	2107932	0	0
40°	1556640	0	0
45°	561106	0	0
50°	116819	0	0
55°	26751	344	0
60°	8486	395	0
65°	1868	934	0
70°	0	1154	577
75°	0	1525	0
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P492246

CATALOG NUMBER: LDA2B058040R20D010 2LBDLC1MB-30DEG TILT

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.9	0.4
10°-20°	29.3	5.5
20°-30°	197.7	37.0
30°-40°	230.9	43.3
40°-50°	67.3	12.6
50°-60°	4.5	0.8
60°-70°	0.8	0.2
70°-80°	0.7	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.9	42.9
0°-40°	459.9	86.2
0°-60°	531.7	99.6
0°-90°	533.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	17	17	17	17	17	
5°	33	24	15	13	11	4
15°	442	50	10	5	3	231
25°	3772	77	2	0	0	1670
35°	3500	42	0	0	0	2150
45°	804	9	0	0	0	741
55°	31	2	0	0	0	40
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P492246

CATALOG NUMBER: LDA2B058040R20D010 2LBDLC1MB-30DEG TILT

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2
2.5°	22.1	22.1	19.6	17.6	16.0	15.1	14.7	13.9	13.5
5°	32.7	28.6	23.7	18.4	15.1	13.9	12.7	11.5	11.0
7.5°	47.9	41.7	28.6	18.8	14.3	12.3	11.0	9.8	9.0
10°	77.3	60.2	35.2	18.8	13.1	10.6	9.0	7.8	7.4
12.5°	142.8	92.1	42.2	18.4	11.9	9.0	7.0	6.1	4.9
15°	442.0	190.7	49.9	17.6	10.2	7.0	5.3	3.3	2.9
17.5°	1143.0	445.3	55.7	15.6	8.2	4.9	2.5	2.0	2.0
20°	2144.9	807.5	63.8	13.5	6.1	3.3	1.6	1.2	0.8
21°	2446.9	987.9	67.9	12.7	5.3	2.0	1.2	0.4	0.4
22°	2916.3	1184.8	71.2	11.9	4.5	1.2	0.8	0.4	0.0
23°	3250.7	1310.4	74.5	10.6	3.3	1.2	0.4	0.0	0.0
24°	3585.0	1470.4	76.5	9.8	2.9	0.8	0.4	0.0	0.0
25°	3772.1	1603.9	77.3	9.0	2.0	0.4	0.0	0.0	0.0
26°	3925.9	1693.1	77.8	8.2	1.2	0.0	0.0	0.0	0.0
27°	4057.7	1796.6	76.9	7.4	1.2	0.0	0.0	0.0	0.0
28°	4132.6	1813.8	75.7	6.5	0.4	0.0	0.0	0.0	0.0
29°	4165.0	1792.9	72.0	5.7	0.4	0.0	0.0	0.0	0.0
30°	4227.6	1773.3	68.3	5.3	0.0	0.0	0.0	0.0	0.0
31°	4169.9	1708.2	63.8	4.5	0.0	0.0	0.0	0.0	0.0
32°	3944.0	1653.4	58.5	3.7	0.0	0.0	0.0	0.0	0.0
33°	3876.4	1540.8	52.8	3.3	0.0	0.0	0.0	0.0	0.0
34°	3749.2	1373.4	47.9	2.9	0.0	0.0	0.0	0.0	0.0
35°	3499.9	1235.1	41.7	2.5	0.0	0.0	0.0	0.0	0.0
36°	3326.0	1077.1	36.4	2.0	0.0	0.0	0.0	0.0	0.0
37°	3143.9	939.2	32.3	1.6	0.0	0.0	0.0	0.0	0.0
38°	2917.6	794.4	27.4	1.2	0.0	0.0	0.0	0.0	0.0
39°	2654.0	656.4	23.3	1.2	0.0	0.0	0.0	0.0	0.0
40°	2417.0	529.2	20.1	0.8	0.0	0.0	0.0	0.0	0.0
42.5°	1491.7	302.0	11.9	0.8	0.0	0.0	0.0	0.0	0.0
45°	804.2	183.3	8.6	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	370.4	85.5	6.1	0.4	0.0	0.0	0.0	0.0	0.0
50°	152.2	38.1	4.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	54.8	21.3	2.9	0.0	0.0	0.4	0.0	0.0	0.0
55°	31.1	12.3	1.6	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	14.7	7.0	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	8.6	3.7	0.4	0.4	0.4	0.8	0.4	0.0	0.0
62.5°	4.1	1.2	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.0
67.5°	0.4	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
70°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
72.5°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
77.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P492246

CATALOG NUMBER: LDA2B058040R20D010 2LBDLC1MB-30DEG TILT

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)