

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494363

Luminaire Tested: **LDA2B059730R70D010 2LBDL1WH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494363  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059730R70D010 2LBDL1WH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 522.7 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494363

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P494363

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		81	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	206965
5°	205725
10°	204397
15°	200578
20°	193314
25°	185084
30°	176318
35°	145451
40°	94545
45°	49399
50°	22949
55°	8429
60°	888
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P494363

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.3	7.5
10°-20°	110.4	21.1
20°-30°	156.6	30.0
30°-40°	146.5	28.0
40°-50°	58.9	11.3
50°-60°	10.3	2.0
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.3	58.6
0°-40°	452.7	86.6
0°-60°	521.9	99.8
0°-90°	522.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	522.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	420	
5°	415	39
15°	393	110
25°	340	157
35°	242	146
45°	71	59
55°	10	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494363

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	419.5
1°	420.0
2°	419.2
3°	417.5
4°	416.6
5°	415.4
6°	410.8
7°	412.3
8°	408.2
9°	407.4
10°	408.0
11°	404.2
12°	403.3
13°	398.7
14°	397.0
15°	392.7
16°	390.1
17°	384.9
18°	378.9
19°	375.4
20°	368.2
21°	362.8
22.5°	352.7
23°	350.1
24°	345.2
25°	340.0
26°	336.0
27°	330.2
28°	324.5
29°	317.6
30°	309.5
32.5°	281.3
35°	241.5
37.5°	194.6
40°	146.8
42.5°	104.8
45°	70.8
47.5°	46.6
50°	29.9
52.5°	18.7
55°	9.8
57.5°	3.2
60°	0.9
62.5°	0.6
65°	0.6



TEST NUMBER: P494363

CATALOG NUMBER: LDA2B059730R70D010 2LBDL1WH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)