

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492316

Luminaire Tested: **LDA2B058040R35D010 2LBDL1B**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-29)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058040R35D010 2LBDL1B
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 782.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.51
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492316
CATALOG NUMBER: LDA2B058040R35D010 2LBDL1B

Luminous Intensity Polar Plot





TEST NUMBER: P492316

CATALOG NUMBER: LDA2B058040R35D010 2LBDL1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 96 | | | | 96 |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 97 | 95 | 94 | 92 | | | | 92 |
| 3 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 95 | 93 | 96 | 93 | 91 | 94 | 92 | 90 | 89 | | | | 89 |
| 4 | 103 | 97 | 93 | 90 | 102 | 96 | 92 | 89 | 94 | 91 | 88 | 92 | 90 | 87 | 91 | 88 | 87 | 85 | | | | 85 |
| 5 | 100 | 93 | 89 | 86 | 98 | 93 | 88 | 85 | 91 | 87 | 85 | 89 | 86 | 84 | 88 | 85 | 83 | 82 | | | | 82 |
| 6 | 96 | 90 | 85 | 82 | 95 | 89 | 85 | 82 | 88 | 84 | 81 | 86 | 83 | 81 | 85 | 82 | 80 | 79 | | | | 79 |
| 7 | 93 | 86 | 82 | 79 | 92 | 86 | 82 | 79 | 85 | 81 | 78 | 84 | 80 | 78 | 83 | 80 | 77 | 76 | | | | 76 |
| 8 | 90 | 83 | 79 | 76 | 89 | 83 | 79 | 76 | 82 | 78 | 75 | 81 | 78 | 75 | 80 | 77 | 75 | 74 | | | | 74 |
| 9 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 79 | 76 | 73 | 79 | 75 | 73 | 78 | 75 | 72 | 71 | | | | 71 |
| 10 | 85 | 78 | 74 | 71 | 84 | 78 | 73 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 76 | 72 | 70 | 69 | | | | 69 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1193689 |
| 5° | 1154073 |
| 10° | 1008508 |
| 15° | 705061 |
| 20° | 370195 |
| 25° | 159063 |
| 30° | 72749 |
| 35° | 35234 |
| 40° | 17904 |
| 45° | 9140 |
| 50° | 4989 |
| 55° | 2150 |
| 60° | 789 |
| 65° | 467 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P492316

CATALOG NUMBER: LDA2B058040R35D010 2LBDL1B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 212.4 | 27.2 |
| 10°-20° | 368.4 | 47.1 |
| 20°-30° | 147.0 | 18.8 |
| 30°-40° | 40.1 | 5.1 |
| 40°-50° | 11.1 | 1.4 |
| 50°-60° | 2.6 | 0.3 |
| 60°-70° | 0.5 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 727.8 | 93.1 |
| 0°-40° | 767.8 | 98.2 |
| 0°-60° | 781.6 | 99.9 |
| 0°-90° | 782.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 782.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2420 | |
| 5° | 2330 | 212 |
| 15° | 1380 | 368 |
| 25° | 292 | 147 |
| 35° | 58 | 40 |
| 45° | 13 | 11 |
| 55° | 2 | 3 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P492316

CATALOG NUMBER: LDA2B058040R35D010 2LBDL1B

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2419.5 |
| 1° | 2409.3 |
| 2° | 2399.4 |
| 3° | 2384.7 |
| 4° | 2362.6 |
| 5° | 2330.3 |
| 6° | 2288.1 |
| 7° | 2235.7 |
| 8° | 2176.0 |
| 9° | 2093.3 |
| 10° | 2013.1 |
| 11° | 1913.7 |
| 12° | 1786.4 |
| 13° | 1658.3 |
| 14° | 1527.7 |
| 15° | 1380.4 |
| 16° | 1235.5 |
| 17° | 1086.6 |
| 18° | 952.7 |
| 19° | 826.3 |
| 20° | 705.1 |
| 21° | 593.8 |
| 22.5° | 460.4 |
| 23° | 417.4 |
| 24° | 350.3 |
| 25° | 292.2 |
| 26° | 246.0 |
| 27° | 205.4 |
| 28° | 173.9 |
| 29° | 148.1 |
| 30° | 127.7 |
| 32.5° | 85.5 |
| 35° | 58.5 |
| 37.5° | 40.9 |
| 40° | 27.8 |
| 42.5° | 18.8 |
| 45° | 13.1 |
| 47.5° | 9.4 |
| 50° | 6.5 |
| 52.5° | 4.5 |
| 55° | 2.5 |
| 57.5° | 1.2 |
| 60° | 0.8 |
| 62.5° | 0.8 |
| 65° | 0.4 |



TEST NUMBER: P492316

CATALOG NUMBER: LDA2B058040R35D010 2LBDL1B

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 67.5° | 0.4 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)