

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492420

Luminaire Tested: **LDA2B058040R70D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058040R70D010 2LBDL1WHH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 4000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 743.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492420

CATALOG NUMBER: LDA2B058040R70D010 2LBDL1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P492420

CATALOG NUMBER: LDA2B058040R70D010 2LBDL1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294192
5°	292492
10°	290514
15°	285109
20°	274798
25°	263091
30°	250604
35°	206824
40°	134411
45°	70260
50°	32697
55°	11956
60°	1184
65°	934
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P492420

CATALOG NUMBER: LDA2B058040R70D010 2LBDL1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	7.5
10°-20°	156.9	21.1
20°-30°	222.6	30.0
30°-40°	208.2	28.0
40°-50°	83.8	11.3
50°-60°	14.6	2.0
60°-70°	0.7	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.4	58.6
0°-40°	643.6	86.6
0°-60°	742.0	99.9
0°-90°	743.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	596	
5°	591	56
15°	558	157
25°	483	223
35°	343	208
45°	101	84
55°	14	15
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492420

CATALOG NUMBER: LDA2B058040R70D010 2LBDL1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	596.3
1°	597.1
2°	595.9
3°	593.4
4°	592.2
5°	590.6
6°	584.0
7°	586.0
8°	580.3
9°	579.1
10°	579.9
11°	574.6
12°	573.4
13°	566.8
14°	564.4
15°	558.2
16°	554.5
17°	547.2
18°	538.6
19°	533.7
20°	523.4
21°	515.7
22.5°	501.3
23°	497.7
24°	490.7
25°	483.3
26°	477.6
27°	469.4
28°	461.2
29°	451.4
30°	439.9
32.5°	399.8
35°	343.4
37.5°	276.7
40°	208.7
42.5°	149.0
45°	100.7
47.5°	66.3
50°	42.6
52.5°	26.6
55°	13.9
57.5°	4.5
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P492420

CATALOG NUMBER: LDA2B058040R70D010 2LBDL1WHH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)