

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280306

Luminaire Tested: **LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, H
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 634.6 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280306

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H

Luminous Intensity Polar Plot





TEST NUMBER: P280306

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542007
5°	530954
10°	493759
15°	431086
20°	356912
25°	272999
30°	149371
35°	55290
40°	19128
45°	8652
50°	4068
55°	2064
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280306

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	15.7
10°-20°	233.3	36.8
20°-30°	220.5	34.7
30°-40°	67.9	10.7
40°-50°	10.7	1.7
50°-60°	2.3	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.4	87.2
0°-40°	621.3	97.9
0°-60°	634.3	99.9
0°-90°	634.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	634.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1099	
5°	1072	100
15°	844	233
25°	502	221
35°	92	68
45°	12	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280306

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1098.6
1°	1094.5
2°	1089.5
3°	1085.3
4°	1080.0
5°	1072.1
6°	1061.8
7°	1048.0
8°	1029.4
9°	1007.9
10°	985.6
11°	960.9
12°	934.7
13°	906.1
14°	876.4
15°	844.0
17.5°	758.4
20°	679.8
22.5°	600.1
25°	501.5
27.5°	382.6
30°	262.2
32.5°	161.0
35°	91.8
37.5°	51.2
40°	29.7
42.5°	18.5
45°	12.4
47.5°	8.2
50°	5.3
52.5°	3.5
55°	2.4
57.5°	1.5
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280306

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)