

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280311

Luminaire Tested: **LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 639.2 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280311

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P280311

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95				95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90				90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85				85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80				80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76				76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72				72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69				69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65				65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62				62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	545855
5°	534767
10°	497265
15°	434202
20°	359484
25°	274959
30°	150454
35°	55711
40°	19257
45°	8652
50°	4068
55°	2064
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280311

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	15.7
10°-20°	234.9	36.8
20°-30°	222.1	34.7
30°-40°	68.4	10.7
40°-50°	10.8	1.7
50°-60°	2.3	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.4	87.2
0°-40°	625.7	97.9
0°-60°	638.8	99.9
0°-90°	639.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	639.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1106	
5°	1080	100
15°	850	235
25°	505	222
35°	92	68
45°	12	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280311

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1106.4
1°	1102.3
2°	1097.3
3°	1093.1
4°	1087.8
5°	1079.8
6°	1069.4
7°	1055.5
8°	1036.8
9°	1015.2
10°	992.6
11°	967.7
12°	941.3
13°	912.6
14°	882.7
15°	850.1
17.5°	763.8
20°	684.7
22.5°	604.3
25°	505.1
27.5°	385.3
30°	264.1
32.5°	162.1
35°	92.5
37.5°	51.6
40°	29.9
42.5°	18.7
45°	12.4
47.5°	8.3
50°	5.3
52.5°	3.6
55°	2.4
57.5°	1.5
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280311

CATALOG NUMBER: LDA2B05D2WD010 EU2B05WFL55D2W 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)