

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492429

Luminaire Tested: **LDA2B058050R20D010 2LBD1H-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492429  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058050R20D010 2LBD1H-30DEG TILT  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 530.3 lumens  
Efficiency: N/A  
Efficacy: 75.8 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492429

CATALOG NUMBER: LDA2B058050R20D010 2LBD1H-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P492429

CATALOG NUMBER: LDA2B058050R20D010 2LBD1H-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	8436	8436	8436
5°	16096	7429	5448
10°	38475	6513	3657
15°	224277	5210	1430
20°	1118775	3203	420
25°	2040006	1089	0
30°	2392678	0	0
35°	2094200	0	0
40°	1546529	0	0
45°	557408	0	0
50°	116051	0	0
55°	26579	344	0
60°	8387	395	0
65°	1868	934	0
70°	0	1154	577
75°	0	1525	0
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P492429

CATALOG NUMBER: LDA2B058050R20D010 2LBD1H-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.9	0.4
10°-20°	29.1	5.5
20°-30°	196.4	37.0
30°-40°	229.4	43.3
40°-50°	66.9	12.6
50°-60°	4.5	0.8
60°-70°	0.8	0.2
70°-80°	0.7	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.4	42.9
0°-40°	456.9	86.2
0°-60°	528.3	99.6
0°-90°	530.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.3	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	17	17	17	17	17	
5°	32	24	15	13	11	4
15°	439	50	10	5	3	229
25°	3748	77	2	0	0	1659
35°	3477	42	0	0	0	2136
45°	799	8	0	0	0	736
55°	31	2	0	0	0	39
65°	2	1	1	1	0	3
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P492429

CATALOG NUMBER: LDA2B058050R20D010 2LBD1H-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1
2.5°	22.0	22.0	19.5	17.5	15.9	15.0	14.6	13.8	13.4
5°	32.5	28.5	23.6	18.3	15.0	13.8	12.6	11.4	11.0
7.5°	47.6	41.5	28.5	18.7	14.2	12.2	11.0	9.8	8.9
10°	76.8	59.8	35.0	18.7	13.0	10.6	8.9	7.7	7.3
12.5°	141.9	91.5	41.9	18.3	11.8	8.9	6.9	6.1	4.9
15°	439.1	189.5	49.6	17.5	10.2	6.9	5.3	3.3	2.8
17.5°	1135.6	442.4	55.3	15.5	8.1	4.9	2.4	2.0	2.0
20°	2130.9	802.2	63.4	13.4	6.1	3.3	1.6	1.2	0.8
21°	2431.0	981.5	67.5	12.6	5.3	2.0	1.2	0.4	0.4
22°	2897.3	1177.1	70.7	11.8	4.5	1.2	0.8	0.4	0.0
23°	3229.5	1301.9	74.0	10.6	3.3	1.2	0.4	0.0	0.0
24°	3561.7	1460.9	76.0	9.8	2.8	0.8	0.4	0.0	0.0
25°	3747.5	1593.4	76.8	8.9	2.0	0.4	0.0	0.0	0.0
26°	3900.4	1682.0	77.3	8.1	1.2	0.0	0.0	0.0	0.0
27°	4031.3	1784.9	76.4	7.3	1.2	0.0	0.0	0.0	0.0
28°	4105.7	1802.0	75.2	6.5	0.4	0.0	0.0	0.0	0.0
29°	4137.8	1781.2	71.6	5.7	0.4	0.0	0.0	0.0	0.0
30°	4200.0	1761.7	67.9	5.3	0.0	0.0	0.0	0.0	0.0
31°	4142.7	1697.1	63.4	4.5	0.0	0.0	0.0	0.0	0.0
32°	3918.2	1642.6	58.1	3.7	0.0	0.0	0.0	0.0	0.0
33°	3851.2	1530.8	52.4	3.3	0.0	0.0	0.0	0.0	0.0
34°	3724.7	1364.5	47.6	2.8	0.0	0.0	0.0	0.0	0.0
35°	3477.1	1227.1	41.5	2.4	0.0	0.0	0.0	0.0	0.0
36°	3304.3	1070.1	36.2	2.0	0.0	0.0	0.0	0.0	0.0
37°	3123.4	933.1	32.1	1.6	0.0	0.0	0.0	0.0	0.0
38°	2898.5	789.2	27.2	1.2	0.0	0.0	0.0	0.0	0.0
39°	2636.7	652.2	23.2	1.2	0.0	0.0	0.0	0.0	0.0
40°	2401.3	525.7	19.9	0.8	0.0	0.0	0.0	0.0	0.0
42.5°	1482.0	300.1	11.8	0.8	0.0	0.0	0.0	0.0	0.0
45°	798.9	182.1	8.5	0.4	0.0	0.0	0.0	0.0	0.0
47.5°	368.0	85.0	6.1	0.4	0.0	0.0	0.0	0.0	0.0
50°	151.2	37.8	4.5	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	54.5	21.1	2.8	0.0	0.0	0.4	0.0	0.0	0.0
55°	30.9	12.2	1.6	0.4	0.4	0.4	0.4	0.0	0.0
57.5°	14.6	6.9	0.4	0.4	0.4	0.4	0.4	0.0	0.0
60°	8.5	3.7	0.4	0.4	0.4	0.8	0.4	0.0	0.0
62.5°	4.1	1.2	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.0
67.5°	0.4	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
70°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
72.5°	0.0	0.4	0.8	0.8	0.8	1.2	0.8	0.4	0.4
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
77.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P492429

CATALOG NUMBER: LDA2B058050R20D010 2LBD1H-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)