

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492509

Luminaire Tested: **LDA2B058050R35D010 2LBD1GPH-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492509  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058050R35D010 2LBD1GPH-30DEG TILT  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 577.6 lumens  
Efficiency: N/A  
Efficacy: 82.5 lumens/watt  
Spacing Criteria (0/90/45): 3.16 / 0.51 / 1.46  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492509

CATALOG NUMBER: LDA2B058050R35D010 2LBD1GPH-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P492509

CATALOG NUMBER: LDA2B058050R35D010 2LBD1GPH-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56
6	77	66	58	53	76	65	58	52	63	57	52	62	56	52	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	54	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	36	35
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	9621	9621	9621
5°	30210	8469	5250
10°	128950	7114	3857
15°	416581	5210	3116
20°	858573	3203	2153
25°	1135218	1524	1306
30°	1217645	684	684
35°	1163672	482	241
40°	1086428	258	0
45°	960271	0	0
50°	681878	307	0
55°	244455	344	0
60°	37693	789	0
65°	1868	934	0
70°	0	1154	0
75°	0	1525	762
80°	0	2273	0
85°	0	4529	0



TEST NUMBER: P492509

CATALOG NUMBER: LDA2B058050R35D010 2LBD1GPH-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	3.4	0.6
10°-20°	46.8	8.1
20°-30°	156.5	27.1
30°-40°	197.1	34.1
40°-50°	139.4	24.1
50°-60°	32.2	5.6
60°-70°	1.0	0.2
70°-80°	0.6	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.7	35.8
0°-40°	403.8	69.9
0°-60°	575.4	99.6
0°-90°	577.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	577.6	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	20	20	20	20	20	
5°	61	40	17	12	11	11
15°	816	144	10	7	6	269
25°	2085	228	3	3	2	940
35°	1932	133	1	1	0	1210
45°	1376	33	0	0	0	1032
55°	284	2	0	0	0	322
65°	2	0	1	1	0	6
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P492509

CATALOG NUMBER: LDA2B058050R35D010 2LBD1GPH-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	19.5	19.5	19.5	19.5	19.5	19.5	19.5	19.5	19.5
1°	24.4	23.6	22.4	20.3	18.3	17.5	17.5	16.3	16.3
2°	29.3	28.1	25.6	21.5	18.3	16.3	15.5	14.6	14.2
3°	37.8	34.6	29.3	23.2	17.9	15.5	15.0	13.0	13.0
4°	47.2	43.9	33.7	24.4	17.5	14.6	13.0	12.2	11.8
5°	61.0	53.7	39.8	25.6	17.1	13.8	12.2	11.0	10.6
6°	78.9	68.7	45.5	26.8	16.7	13.0	11.4	10.2	9.8
7°	99.2	85.4	52.4	28.1	15.9	12.2	10.6	9.8	9.4
8°	142.3	109.8	60.6	28.9	15.5	11.4	10.2	8.9	8.5
9°	190.3	141.9	69.5	30.1	14.6	11.0	9.4	8.5	8.1
10°	257.4	185.8	79.7	30.9	14.2	10.2	8.5	8.1	7.7
11°	324.0	240.3	92.3	31.3	13.4	8.9	8.5	8.1	7.7
12°	433.8	292.3	103.3	31.3	12.6	8.5	7.7	7.3	6.9
13°	563.9	381.8	119.1	31.7	11.4	8.1	7.3	6.9	6.9
14°	678.6	461.9	129.7	31.7	11.0	7.3	6.9	6.9	6.5
15°	815.6	539.9	143.9	31.3	10.2	6.9	6.9	6.5	6.1
16°	959.1	657.0	163.0	30.5	9.4	6.1	6.5	5.7	5.3
17°	1149.4	753.8	177.7	29.7	8.5	5.7	5.7	5.7	5.3
18°	1323.4	871.3	189.5	28.9	7.7	5.7	5.3	5.3	4.9
19°	1510.0	965.6	201.3	27.6	6.9	4.9	4.9	4.9	4.5
20°	1635.3	1081.5	214.3	26.4	6.1	4.5	4.9	4.5	4.1
21°	1793.8	1185.2	219.1	25.2	5.3	4.1	4.1	4.1	3.7
22.5°	1942.2	1323.0	226.9	22.8	4.5	3.3	3.7	3.3	3.3
23°	1965.0	1352.3	226.9	22.0	4.1	3.3	3.7	3.3	3.3
24°	2040.6	1432.4	229.7	20.3	3.3	2.8	3.3	2.8	2.8
25°	2085.4	1495.8	227.7	18.7	2.8	2.8	2.8	2.8	2.4
26°	2103.7	1513.3	222.8	17.5	2.4	2.4	2.8	2.4	2.0
27°	2122.8	1553.1	216.7	15.9	2.0	2.4	2.4	2.4	2.0
28°	2136.2	1558.0	210.6	14.6	1.6	2.0	2.4	2.0	2.0
29°	2140.7	1564.5	203.3	13.0	1.2	1.6	2.0	1.6	1.6
30°	2137.4	1563.3	192.7	11.8	1.2	1.6	1.6	1.6	1.2
32.5°	2075.2	1528.3	163.4	8.5	0.8	1.2	1.2	1.2	0.8
35°	1932.1	1447.8	133.4	5.7	0.8	0.8	0.8	0.8	0.4
37.5°	1819.0	1327.5	102.1	3.3	0.4	0.8	0.8	0.4	0.0
40°	1686.9	1153.1	73.6	2.0	0.4	0.4	0.4	0.0	0.0
42.5°	1552.7	975.4	50.0	0.8	0.0	0.4	0.4	0.0	0.0
45°	1376.3	746.9	32.9	0.4	0.0	0.4	0.0	0.0	0.0
47.5°	1157.5	542.4	22.4	0.0	0.0	0.4	0.0	0.0	0.0
50°	888.4	303.7	12.6	0.0	0.4	0.4	0.4	0.0	0.0
52.5°	585.5	151.7	4.9	0.0	0.4	0.4	0.4	0.0	0.0
55°	284.2	81.3	1.6	0.4	0.4	0.8	0.4	0.0	0.0
57.5°	134.2	31.7	0.4	0.4	0.8	0.8	0.4	0.0	0.0
60°	38.2	6.5	0.4	0.4	0.8	0.8	0.4	0.4	0.0
62.5°	5.3	0.8	0.4	0.8	0.8	0.8	0.8	0.4	0.0
65°	1.6	0.4	0.4	0.8	0.8	0.8	0.8	0.4	0.0



TEST NUMBER: P492509

CATALOG NUMBER: LDA2B058050R35D010 2LBD1GPH-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	0.4	0.4	0.4	0.8	0.8	0.8	0.8	0.4	0.0
70°	0.0	0.4	0.4	0.8	0.8	0.8	0.8	0.4	0.0
72.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
75°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.4
77.5°	0.0	0.4	0.8	0.8	1.2	0.8	0.8	0.4	0.0
80°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
82.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
85°	0.0	0.4	0.8	0.8	0.8	0.8	0.8	0.4	0.0
87.5°	0.0	0.4	0.8	0.8	0.8	0.8	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)