

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492564

Luminaire Tested: **LDA2B058050R45D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492564  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058050R45D010 2LBDL1MMS  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 785.3 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492564

CATALOG NUMBER: LDA2B058050R45D010 2LBDL1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P492564

CATALOG NUMBER: LDA2B058050R45D010 2LBDL1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82
5	97	90	85	81	95	89	84	81	87	83	80	86	82	80	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68
9	83	75	70	66	82	74	70	66	74	69	66	73	69	66	72	68	66	65
10	80	72	67	64	79	71	67	64	71	66	63	70	66	63	69	66	63	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	778278
5°	761144
10°	706171
15°	602244
20°	453411
25°	273325
30°	131768
35°	59747
40°	27500
45°	14164
50°	7522
55°	2838
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P492564

CATALOG NUMBER: LDA2B058050R45D010 2LBDL1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.9	18.2
10°-20°	322.0	41.0
20°-30°	230.0	29.3
30°-40°	69.0	8.8
40°-50°	17.1	2.2
50°-60°	3.6	0.5
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.9	88.5
0°-40°	763.9	97.3
0°-60°	784.6	99.9
0°-90°	785.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	785.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1578	
5°	1537	143
15°	1179	322
25°	502	230
35°	99	69
45°	20	17
55°	3	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492564

CATALOG NUMBER: LDA2B058050R45D010 2LBDL1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1577.5
1°	1580.4
2°	1576.7
3°	1563.3
4°	1553.6
5°	1536.9
6°	1520.2
7°	1502.3
8°	1473.1
9°	1445.4
10°	1409.6
11°	1373.8
12°	1328.7
13°	1280.3
14°	1235.2
15°	1179.1
16°	1124.2
17°	1062.0
18°	1003.0
19°	930.7
20°	863.6
21°	789.2
22.5°	678.2
23°	640.8
24°	568.0
25°	502.1
26°	436.3
27°	376.1
28°	320.0
29°	274.0
30°	231.3
32.5°	152.1
35°	99.2
37.5°	65.1
40°	42.7
42.5°	28.9
45°	20.3
47.5°	14.6
50°	9.8
52.5°	6.1
55°	3.3
57.5°	1.6
60°	0.8
62.5°	0.8
65°	0.4



TEST NUMBER: P492564

CATALOG NUMBER: LDA2B058050R45D010 2LBDL1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)