

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P283897

Luminaire Tested: **LDA2B108035D010 EU2B10WFL558035 2LBALPINSQ1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P283897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-61)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108035D010 EU2B10WFL558035 2LBALPINSQ1MMS
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in Adj SQ Pinhole w-lens, MMS

Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 924.4 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.68
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P283897

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALPINSQ1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P283897

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALPINSQ1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89																			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	87	90	87	85	84																			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	81	86	83	81	79																			
5	95	88	82	79	94	87	82	78	85	81	78	83	80	77	82	79	76	75																			
6	91	83	78	74	90	82	77	74	81	77	73	80	76	73	78	75	72	71																			
7	87	79	74	70	86	78	73	70	77	73	69	76	72	69	75	71	69	67																			
8	84	75	70	66	83	75	70	66	74	69	66	73	69	66	72	68	65	64																			
9	81	72	67	63	80	71	66	63	71	66	63	70	66	63	69	65	62	61																			
10	77	69	64	60	76	68	63	60	68	63	60	67	63	60	66	62	60	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	840738	840738	840738
5°	815473	817454	813739
10°	746449	743443	738985
15°	627884	633707	626863
20°	480135	492893	479348
25°	304899	343766	310832
30°	177343	200187	180419
35°	93715	99738	94016
40°	49462	51716	49462
45°	27699	28676	27979
50°	12971	16348	12971
55°	4731	8946	5075
60°	5427	5427	5427
65°	5837	6421	5837
70°	7212	6491	7212
75°	6672	6672	6672
80°	7103	5682	7103
85°	5661	5661	5661



TEST NUMBER: P283897

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALPINSQ1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	16.5
10°-20°	338.7	36.6
20°-30°	273.5	29.6
30°-40°	108.1	11.7
40°-50°	33.2	3.6
50°-60°	8.6	0.9
60°-70°	5.2	0.6
70°-80°	3.8	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	764.3	82.7
0°-40°	872.5	94.4
0°-60°	914.2	98.9
0°-90°	924.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	924.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1704	1704	1704	1704	1704	
5°	1647	1650	1651	1647	1643	152
15°	1229	1233	1241	1236	1227	338
25°	560	587	632	598	571	261
35°	156	160	166	161	156	104
45°	40	40	41	41	40	32
55°	6	7	10	7	6	7
65°	5	6	6	6	5	5
75°	4	4	4	4	4	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P283897

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALPINSQ1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.1	1704.1	1704.1	1704.1	1704.1
2.5°	1682.8	1683.8	1685.3	1683.3	1678.3
5°	1646.6	1649.6	1650.6	1647.1	1643.1
7.5°	1587.1	1583.7	1586.6	1580.7	1575.7
10°	1490.0	1485.5	1484.0	1475.1	1475.1
12.5°	1370.0	1368.5	1369.5	1365.1	1358.1
15°	1229.3	1232.7	1240.7	1235.7	1227.3
17.5°	1080.1	1085.0	1092.0	1090.5	1079.1
20°	914.5	928.9	938.8	929.4	913.0
22.5°	726.2	756.9	782.2	762.3	735.6
25°	560.1	586.9	631.5	597.8	571.0
27.5°	424.8	444.1	484.8	451.6	433.2
30°	311.3	323.2	351.4	329.6	316.7
32.5°	222.6	231.0	242.9	230.0	223.5
35°	155.6	160.1	165.6	160.6	156.1
37.5°	109.5	111.0	115.0	111.0	109.0
40°	76.8	77.3	80.3	77.8	76.8
42.5°	55.5	55.5	57.0	56.0	55.5
45°	39.7	40.1	41.1	40.6	40.1
47.5°	28.3	29.2	29.2	29.7	27.8
50°	16.9	20.8	21.3	20.8	16.9
52.5°	8.9	12.4	15.4	12.4	8.9
55°	5.5	7.4	10.4	7.4	5.9
57.5°	5.5	5.5	6.9	5.9	5.5
60°	5.5	5.5	5.5	5.5	5.5
62.5°	5.5	5.5	5.5	5.5	5.5
65°	5.0	5.5	5.5	5.5	5.0
67.5°	5.0	5.0	5.0	5.0	5.0
70°	5.0	5.0	4.5	5.0	5.0
72.5°	4.5	4.5	4.0	4.5	4.5
75°	3.5	3.5	3.5	3.5	3.5
77.5°	3.0	3.0	3.0	3.0	3.0
80°	2.5	2.5	2.0	2.5	2.5
82.5°	1.5	1.5	1.5	1.5	1.5
85°	1.0	1.0	1.0	1.0	1.0
87.5°	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)