

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492606

Luminaire Tested: **LDA2B058050R65D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B058050R65D010 2LBDL1GPH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 761.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492606

CATALOG NUMBER: LDA2B058050R65D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P492606

CATALOG NUMBER: LDA2B058050R65D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72		79	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58		66	61	57		65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50		59	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	398192
5°	381587
10°	363355
15°	345329
20°	321263
25°	296570
30°	257327
35°	184660
40°	100277
45°	42840
50°	18421
55°	6623
60°	1184
65°	934
70°	577
75°	0
80°	0
85°	0



TEST NUMBER: P492606

CATALOG NUMBER: LDA2B058050R65D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.1	9.5
10°-20°	189.4	24.9
20°-30°	247.6	32.5
30°-40°	188.4	24.8
40°-50°	54.5	7.2
50°-60°	8.2	1.1
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.2	66.9
0°-40°	697.6	91.7
0°-60°	760.2	99.9
0°-90°	761.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	807	
5°	770	72
15°	676	189
25°	545	248
35°	307	188
45°	61	54
55°	8	8
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492606

CATALOG NUMBER: LDA2B058050R65D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	807.1
1°	804.2
2°	799.8
3°	790.8
4°	781.0
5°	770.5
6°	760.3
7°	751.4
8°	742.8
9°	735.1
10°	725.3
11°	716.8
12°	707.9
13°	698.9
14°	689.2
15°	676.1
16°	666.4
17°	654.6
18°	636.7
19°	627.4
20°	611.9
21°	598.1
22.5°	576.9
23°	568.8
24°	556.2
25°	544.8
26°	529.8
27°	513.1
28°	494.8
29°	475.3
30°	451.7
32.5°	387.1
35°	306.6
37.5°	226.1
40°	155.7
42.5°	98.8
45°	61.4
47.5°	38.2
50°	24.0
52.5°	14.2
55°	7.7
57.5°	2.8
60°	1.2
62.5°	0.8
65°	0.8



TEST NUMBER: P492606

CATALOG NUMBER: LDA2B058050R65D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)