

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492639

Luminaire Tested: **LDA2B058050R70D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492639  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B058050R70D010 2LBDLC1MMS  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 797.2 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492639

CATALOG NUMBER: LDA2B058050R70D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P492639

CATALOG NUMBER: LDA2B058050R70D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	315653
5°	313838
10°	311705
15°	305949
20°	294854
25°	282307
30°	268948
35°	221881
40°	144265
45°	75354
50°	35076
55°	12816
60°	1283
65°	1051
70°	577
75°	762
80°	0
85°	0



TEST NUMBER: P492639

CATALOG NUMBER: LDA2B058050R70D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.9	7.5
10°-20°	168.3	21.1
20°-30°	238.9	30.0
30°-40°	223.4	28.0
40°-50°	89.8	11.3
50°-60°	15.7	2.0
60°-70°	0.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.2	58.6
0°-40°	690.5	86.6
0°-60°	796.1	99.9
0°-90°	797.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	640	
5°	634	60
15°	599	168
25°	519	239
35°	368	223
45°	108	90
55°	15	16
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492639

CATALOG NUMBER: LDA2B058050R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	639.8
1°	640.7
2°	639.4
3°	636.7
4°	635.4
5°	633.7
6°	626.6
7°	628.8
8°	622.7
9°	621.4
10°	622.2
11°	616.5
12°	615.2
13°	608.2
14°	605.6
15°	599.0
16°	595.0
17°	587.1
18°	577.9
19°	572.6
20°	561.6
21°	553.3
22.5°	537.9
23°	534.0
24°	526.5
25°	518.6
26°	512.5
27°	503.7
28°	494.9
29°	484.4
30°	472.1
32.5°	429.0
35°	368.4
37.5°	296.8
40°	224.0
42.5°	159.8
45°	108.0
47.5°	71.1
50°	45.7
52.5°	28.5
55°	14.9
57.5°	4.8
60°	1.3
62.5°	0.9
65°	0.9



TEST NUMBER: P492639

CATALOG NUMBER: LDA2B058050R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)