

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279283

Luminaire Tested: **LDA2B059024D010 EU2B05FL409024 2LBAD1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059024D010 EU2B05FL409024 2LBAD1LI
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 619.7 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279283

CATALOG NUMBER: LDA2B059024D010 EU2B05FL409024 2LBAD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P279283

CATALOG NUMBER: LDA2B059024D010 EU2B05FL409024 2LBAD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																			
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	852036
5°	833995
10°	760126
15°	593816
20°	351557
25°	130702
30°	40846
35°	18189
40°	8437
45°	3977
50°	2149
55°	1204
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279283

CATALOG NUMBER: LDA2B059024D010 EU2B05FL409024 2LBAD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.7	25.1
10°-20°	309.6	50.0
20°-30°	126.8	20.5
30°-40°	21.0	3.4
40°-50°	5.0	0.8
50°-60°	1.3	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.0	95.5
0°-40°	613.0	98.9
0°-60°	619.3	99.9
0°-90°	619.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	619.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1727	
5°	1684	156
15°	1163	310
25°	240	127
35°	30	21
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279283

CATALOG NUMBER: LDA2B059024D010 EU2B05FL409024 2LBAD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1727.0
1°	1721.0
2°	1713.1
3°	1705.9
4°	1696.6
5°	1684.0
6°	1665.5
7°	1641.4
8°	1606.9
9°	1565.1
10°	1517.3
11°	1461.9
12°	1399.3
13°	1327.9
14°	1248.5
15°	1162.6
17.5°	922.0
20°	669.6
22.5°	428.7
25°	240.1
27.5°	126.6
30°	71.7
32.5°	45.5
35°	30.2
37.5°	19.9
40°	13.1
42.5°	8.5
45°	5.7
47.5°	4.0
50°	2.8
52.5°	2.0
55°	1.4
57.5°	0.9
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279283

CATALOG NUMBER: LDA2B059024D010 EU2B05FL409024 2LBAD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)