

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278399

Luminaire Tested: **LDA2B059024D010 EU2B05NFL259024 2LBALD1WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P278399  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B059024D010 EU2B05NFL259024 2LBALD1WH  
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC  
AND 2in ADJ spun Refl w/lens Self-Flanged, WH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 558.3 lumens  
Efficiency: N/A  
Efficacy: 79.8 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P278399

CATALOG NUMBER: LDA2B059024D010 EU2B05NFL259024 2LBALD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P278399

CATALOG NUMBER: LDA2B059024D010 EU2B05NFL259024 2LBALD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1428924
5°	1317801
10°	888024
15°	437828
20°	187014
25°	73544
30°	28940
35°	12708
40°	6118
45°	2930
50°	1612
55°	946
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P278399

CATALOG NUMBER: LDA2B059024D010 EU2B05NFL259024 2LBALD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	225.4	40.4
10°-20°	242.8	43.5
20°-30°	70.1	12.6
30°-40°	14.8	2.7
40°-50°	3.6	0.7
50°-60°	1.1	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.2	96.4
0°-40°	553.0	99.1
0°-60°	557.7	99.9
0°-90°	558.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2896	
5°	2661	225
15°	857	243
25°	135	70
35°	21	15
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278399

CATALOG NUMBER: LDA2B059024D010 EU2B05NFL259024 2LBALD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2896.3
1°	2878.1
2°	2847.3
3°	2805.7
4°	2746.8
5°	2660.9
6°	2545.1
7°	2394.0
8°	2208.1
9°	1991.4
10°	1772.6
11°	1551.5
12°	1342.7
13°	1157.4
14°	994.4
15°	857.2
17.5°	566.6
20°	356.2
22.5°	219.0
25°	135.1
27.5°	82.4
30°	50.8
32.5°	32.1
35°	21.1
37.5°	14.0
40°	9.5
42.5°	6.6
45°	4.2
47.5°	2.6
50°	2.1
52.5°	1.6
55°	1.1
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P278399

CATALOG NUMBER: LDA2B059024D010 EU2B05NFL259024 2LBALD1WH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)