

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280180

Luminaire Tested: **LDA2B059024D010 EU2B05WFL559024 2LBAD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059024D010 EU2B05WFL559024 2LBAD1MW
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280180

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P280180

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95	95	93	95	93	91	95	93	91	90	95																										
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90	95	93	91	90	95	93	91	90	95																											
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85	85	83	87	84	82	87	84	82	80	85																										
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	85	83	87	84	82	80	76	74	72	76																										
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	83	80	78	76	74	72	70	69	76																											
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72	80	76	74	72	70	68	67	73	69	67	65																									
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69	76	73	70	68	67	65	63	62	69																											
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	73	69	67	65	63	61	60	65	61	59																										
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62	70	66	64	62	60	58	57	63	59	57																										
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59	67	63	61	59	57	55	53	59	55	53																										

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	523556
5°	512877
10°	476926
15°	416427
20°	344784
25°	263690
30°	144301
35°	53423
40°	18484
45°	8303
50°	3914
55°	1978
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280180

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	15.7
10°-20°	225.3	36.8
20°-30°	213.0	34.7
30°-40°	65.6	10.7
40°-50°	10.4	1.7
50°-60°	2.2	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.5	87.2
0°-40°	600.1	97.9
0°-60°	612.7	99.9
0°-90°	613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1061	
5°	1036	96
15°	815	225
25°	484	213
35°	89	66
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280180

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1061.2
1°	1057.2
2°	1052.4
3°	1048.4
4°	1043.3
5°	1035.6
6°	1025.6
7°	1012.3
8°	994.4
9°	973.6
10°	952.0
11°	928.1
12°	902.8
13°	875.3
14°	846.6
15°	815.3
17.5°	732.6
20°	656.7
22.5°	579.6
25°	484.4
27.5°	369.5
30°	253.3
32.5°	155.5
35°	88.7
37.5°	49.5
40°	28.7
42.5°	17.9
45°	11.9
47.5°	8.0
50°	5.1
52.5°	3.4
55°	2.3
57.5°	1.4
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280180

CATALOG NUMBER: LDA2B059024D010 EU2B05WFL559024 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)