

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492696

Luminaire Tested: **LDA2B059024R30D010 2LBD1MW**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-14)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059024R30D010 2LBD1MW
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 532.6 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492696

CATALOG NUMBER: LDA2B059024R30D010 2LBD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P492696

CATALOG NUMBER: LDA2B059024R30D010 2LBD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1032014
5°	984005
10°	797999
15°	487832
20°	213160
25°	79749
30°	33042
35°	15479
40°	7213
45°	3489
50°	1919
55°	688
60°	296
65°	350
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P492696

CATALOG NUMBER: LDA2B059024R30D010 2LBD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.2	33.3
10°-20°	255.9	48.1
20°-30°	76.4	14.3
30°-40°	17.5	3.3
40°-50°	4.3	0.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.5	95.7
0°-40°	527.1	99.0
0°-60°	532.4	100.0
0°-90°	532.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2092	
5°	1987	177
15°	955	256
25°	146	76
35°	26	18
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492696

CATALOG NUMBER: LDA2B059024R30D010 2LBD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2091.8
1°	2087.0
2°	2065.8
3°	2051.6
4°	2025.1
5°	1986.9
6°	1934.7
7°	1872.5
8°	1793.2
9°	1696.7
10°	1592.9
11°	1481.9
12°	1355.7
13°	1220.1
14°	1091.2
15°	955.1
16°	823.4
17°	693.6
18°	589.0
19°	487.4
20°	406.0
21°	329.0
22.5°	243.9
23°	219.9
24°	180.0
25°	146.5
26°	120.3
27°	100.2
28°	82.6
29°	69.2
30°	58.0
32.5°	37.9
35°	25.7
37.5°	17.0
40°	11.2
42.5°	7.3
45°	5.0
47.5°	3.6
50°	2.5
52.5°	1.7
55°	0.8
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3



TEST NUMBER: P492696

CATALOG NUMBER: LDA2B059024R30D010 2LBD1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)