

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492789

Luminaire Tested: **LDA2B059024R60D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492789  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059024R60D010 2LBD1GPH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 550.7 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492789

CATALOG NUMBER: LDA2B059024R60D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P492789

CATALOG NUMBER: LDA2B059024R60D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	67	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	329664
5°	312996
10°	306395
15°	296551
20°	271175
25°	240718
30°	180077
35°	101665
40°	38256
45°	17164
50°	8366
55°	1720
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P492789

CATALOG NUMBER: LDA2B059024R60D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.8	10.9
10°-20°	161.3	29.3
20°-30°	197.0	35.8
30°-40°	107.5	19.5
40°-50°	21.5	3.9
50°-60°	3.1	0.6
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.1	75.9
0°-40°	525.6	95.4
0°-60°	550.2	99.9
0°-90°	550.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	550.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	668	
5°	632	60
15°	581	161
25°	442	197
35°	169	107
45°	25	22
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492789

CATALOG NUMBER: LDA2B059024R60D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	668.2
1°	665.2
2°	659.3
3°	651.5
4°	640.3
5°	632.0
6°	627.5
7°	622.2
8°	618.0
9°	616.1
10°	611.6
11°	606.6
12°	602.1
13°	596.8
14°	589.0
15°	580.6
16°	570.0
17°	555.2
18°	545.8
19°	530.4
20°	516.5
21°	503.6
22.5°	482.1
23°	473.2
24°	459.5
25°	442.2
26°	420.2
27°	397.0
28°	370.5
29°	345.4
30°	316.1
32.5°	242.5
35°	168.8
37.5°	105.7
40°	59.4
42.5°	37.1
45°	24.6
47.5°	16.7
50°	10.9
52.5°	5.6
55°	2.0
57.5°	0.8
60°	0.6
62.5°	0.6
65°	0.3



TEST NUMBER: P492789

CATALOG NUMBER: LDA2B059024R60D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)