

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492798

Luminaire Tested: **LDA2B059024R60D010 2LBDL1B**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492798  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059024R60D010 2LBDL1B  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 508.0 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492798  
CATALOG NUMBER: LDA2B059024R60D010 2LBDL1B

### Luminous Intensity Polar Plot





TEST NUMBER: P492798

CATALOG NUMBER: LDA2B059024R60D010 2LBDL1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	90	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	88	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54		61	57	54		61	57	53	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	300655
5°	292790
10°	284753
15°	270655
20°	247287
25°	212357
30°	157974
35°	92752
40°	44181
45°	20652
50°	10285
55°	3613
60°	789
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P492798

CATALOG NUMBER: LDA2B059024R60D010 2LBDL1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.6	11.0
10°-20°	147.4	29.0
20°-30°	175.1	34.5
30°-40°	98.8	19.4
40°-50°	25.7	5.1
50°-60°	4.7	0.9
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.1	74.4
0°-40°	476.9	93.9
0°-60°	507.3	99.9
0°-90°	508.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	508.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	609	
5°	591	56
15°	530	147
25°	390	175
35°	154	99
45°	30	26
55°	4	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492798

CATALOG NUMBER: LDA2B059024R60D010 2LBDL1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	609.4
1°	609.7
2°	605.5
3°	601.8
4°	594.9
5°	591.2
6°	584.8
7°	580.1
8°	575.6
9°	572.5
10°	568.4
11°	560.3
12°	552.7
13°	548.5
14°	538.8
15°	529.9
16°	519.5
17°	507.3
18°	495.5
19°	481.6
20°	471.0
21°	456.5
22.5°	432.5
23°	428.3
24°	407.9
25°	390.1
26°	370.3
27°	347.4
28°	324.8
29°	302.7
30°	277.3
32.5°	213.4
35°	154.0
37.5°	105.2
40°	68.6
42.5°	44.9
45°	29.6
47.5°	20.1
50°	13.4
52.5°	8.4
55°	4.2
57.5°	1.7
60°	0.8
62.5°	0.6
65°	0.6



TEST NUMBER: P492798

CATALOG NUMBER: LDA2B059024R60D010 2LBDL1B

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)