

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492844

Luminaire Tested: **LDA2B059024R70D010 2LBDL1B**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P492844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059024R70D010 2LBDL1B
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 506.6 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P492844
CATALOG NUMBER: LDA2B059024R70D010 2LBDL1B

Luminous Intensity Polar Plot





TEST NUMBER: P492844

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	200552
5°	199386
10°	198085
15°	194397
20°	187381
25°	179368
30°	170849
35°	140995
40°	91647
45°	47864
50°	22259
55°	8171
60°	789
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P492844

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.1	7.5
10°-20°	107.0	21.1
20°-30°	151.8	30.0
30°-40°	141.9	28.0
40°-50°	57.1	11.3
50°-60°	10.0	2.0
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.8	58.6
0°-40°	438.8	86.6
0°-60°	505.8	99.8
0°-90°	506.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	506.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	406	
5°	403	38
15°	381	107
25°	330	152
35°	234	142
45°	69	57
55°	10	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492844

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	406.5
1°	407.1
2°	406.2
3°	404.6
4°	403.7
5°	402.6
6°	398.2
7°	399.6
8°	395.6
9°	394.8
10°	395.4
11°	391.7
12°	390.9
13°	386.4
14°	384.8
15°	380.6
16°	378.1
17°	373.0
18°	367.2
19°	363.8
20°	356.9
21°	351.6
22.5°	341.8
23°	339.3
24°	334.5
25°	329.5
26°	325.6
27°	320.0
28°	314.5
29°	307.8
30°	299.9
32.5°	272.6
35°	234.1
37.5°	188.6
40°	142.3
42.5°	101.6
45°	68.6
47.5°	45.2
50°	29.0
52.5°	18.1
55°	9.5
57.5°	3.1
60°	0.8
62.5°	0.6
65°	0.6



TEST NUMBER: P492844

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)