

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492850

Luminaire Tested: **LDA2B059024R70D010 2LBDL1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059024R70D010 2LBDL1MW  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2400K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 506.6 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492850  
CATALOG NUMBER: LDA2B059024R70D010 2LBDL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P492850

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		81	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	200552
5°	199386
10°	198085
15°	194397
20°	187381
25°	179368
30°	170849
35°	140995
40°	91647
45°	47864
50°	22259
55°	8171
60°	789
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P492850

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.1	7.5
10°-20°	107.0	21.1
20°-30°	151.8	30.0
30°-40°	141.9	28.0
40°-50°	57.1	11.3
50°-60°	10.0	2.0
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.8	58.6
0°-40°	438.8	86.6
0°-60°	505.8	99.8
0°-90°	506.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	506.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	406	
5°	403	38
15°	381	107
25°	330	152
35°	234	142
45°	69	57
55°	10	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P492850

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	406.5
1°	407.1
2°	406.2
3°	404.6
4°	403.7
5°	402.6
6°	398.2
7°	399.6
8°	395.6
9°	394.8
10°	395.4
11°	391.7
12°	390.9
13°	386.4
14°	384.8
15°	380.6
16°	378.1
17°	373.0
18°	367.2
19°	363.8
20°	356.9
21°	351.6
22.5°	341.8
23°	339.3
24°	334.5
25°	329.5
26°	325.6
27°	320.0
28°	314.5
29°	307.8
30°	299.9
32.5°	272.6
35°	234.1
37.5°	188.6
40°	142.3
42.5°	101.6
45°	68.6
47.5°	45.2
50°	29.0
52.5°	18.1
55°	9.5
57.5°	3.1
60°	0.8
62.5°	0.6
65°	0.6



TEST NUMBER: P492850

CATALOG NUMBER: LDA2B059024R70D010 2LBDL1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)