

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P492877

Luminaire Tested: **LDA2B059027R20D010 2LBDC1MB-30DEG TILT**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P492877  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059027R20D010 2LBDC1MB-30DEG TILT  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 392.1 lumens  
Efficiency: N/A  
Efficacy: 56.0 lumens/watt  
Spacing Criteria (0/90/45): 2.56 / 0.56 / 1.2  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P492877

CATALOG NUMBER: LDA2B059027R20D010 2LBDC1MB-30DEG TILT

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P492877

CATALOG NUMBER: LDA2B059027R20D010 2LBDC1MB-30DEG TILT

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91					91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82					82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74					74			
4	92	83	76	71	90	82	75	70	79	74	70	77	73	69	75	71	68	66					66			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59					59			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53					53			
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48					48			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43					43			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38					38			
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34					34			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	6216	6216	6216
5°	11935	5497	4011
10°	28455	4809	2705
15°	165846	3831	1073
20°	827229	2363	315
25°	1508434	817	0
30°	1769214	0	0
35°	1548531	0	0
40°	1143554	0	0
45°	412212	0	0
50°	85810	0	0
55°	19611	258	0
60°	6216	296	0
65°	1401	700	0
70°	0	865	433
75°	0	1144	0
80°	0	1705	0
85°	0	3396	0



TEST NUMBER: P492877

CATALOG NUMBER: LDA2B059027R20D010 2LBDC1MB-30DEG TILT

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.4	0.4
10°-20°	21.5	5.5
20°-30°	145.2	37.0
30°-40°	169.7	43.3
40°-50°	49.5	12.6
50°-60°	3.3	0.8
60°-70°	0.6	0.2
70°-80°	0.5	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.2	42.9
0°-40°	337.8	86.2
0°-60°	390.6	99.6
0°-90°	392.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	392.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	13	13	13	13	13	
5°	24	17	11	9	8	3
15°	325	37	8	4	2	169
25°	2771	57	2	0	0	1227
35°	2571	31	0	0	0	1579
45°	591	6	0	0	0	544
55°	23	1	0	0	0	29
65°	1	1	1	1	0	2
75°	0	1	1	1	0	0
85°	0	1	1	1	0	0
90°	0	0	0	0	0	



TEST NUMBER: P492877

CATALOG NUMBER: LDA2B059027R20D010 2LBDC1MB-30DEG TILT

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.6
2.5°	16.2	16.2	14.4	12.9	11.7	11.1	10.8	10.2	9.9
5°	24.1	21.0	17.4	13.5	11.1	10.2	9.3	8.4	8.1
7.5°	35.2	30.7	21.0	13.8	10.5	9.0	8.1	7.2	6.6
10°	56.8	44.2	25.9	13.8	9.6	7.8	6.6	5.7	5.4
12.5°	104.9	67.6	31.0	13.5	8.7	6.6	5.1	4.5	3.6
15°	324.7	140.1	36.7	12.9	7.5	5.1	3.9	2.4	2.1
17.5°	839.7	327.1	40.9	11.4	6.0	3.6	1.8	1.5	1.5
20°	1575.6	593.2	46.9	9.9	4.5	2.4	1.2	0.9	0.6
21°	1797.5	725.7	49.9	9.3	3.9	1.5	0.9	0.3	0.3
22°	2142.3	870.3	52.3	8.7	3.3	0.9	0.6	0.3	0.0
23°	2388.0	962.6	54.7	7.8	2.4	0.9	0.3	0.0	0.0
24°	2633.6	1080.2	56.2	7.2	2.1	0.6	0.3	0.0	0.0
25°	2771.0	1178.2	56.8	6.6	1.5	0.3	0.0	0.0	0.0
26°	2884.0	1243.7	57.1	6.0	0.9	0.0	0.0	0.0	0.0
27°	2980.8	1319.8	56.5	5.4	0.9	0.0	0.0	0.0	0.0
28°	3035.8	1332.4	55.6	4.8	0.3	0.0	0.0	0.0	0.0
29°	3059.6	1317.1	52.9	4.2	0.3	0.0	0.0	0.0	0.0
30°	3105.6	1302.7	50.2	3.9	0.0	0.0	0.0	0.0	0.0
31°	3063.2	1254.9	46.9	3.3	0.0	0.0	0.0	0.0	0.0
32°	2897.2	1214.6	43.0	2.7	0.0	0.0	0.0	0.0	0.0
33°	2847.6	1131.9	38.8	2.4	0.0	0.0	0.0	0.0	0.0
34°	2754.1	1008.9	35.2	2.1	0.0	0.0	0.0	0.0	0.0
35°	2571.1	907.3	30.7	1.8	0.0	0.0	0.0	0.0	0.0
36°	2443.3	791.3	26.8	1.5	0.0	0.0	0.0	0.0	0.0
37°	2309.5	690.0	23.8	1.2	0.0	0.0	0.0	0.0	0.0
38°	2143.2	583.5	20.1	0.9	0.0	0.0	0.0	0.0	0.0
39°	1949.6	482.2	17.1	0.9	0.0	0.0	0.0	0.0	0.0
40°	1775.6	388.7	14.7	0.6	0.0	0.0	0.0	0.0	0.0
42.5°	1095.8	221.9	8.7	0.6	0.0	0.0	0.0	0.0	0.0
45°	590.8	134.7	6.3	0.3	0.0	0.0	0.0	0.0	0.0
47.5°	272.1	62.8	4.5	0.3	0.0	0.0	0.0	0.0	0.0
50°	111.8	28.0	3.3	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	40.3	15.6	2.1	0.0	0.0	0.3	0.0	0.0	0.0
55°	22.8	9.0	1.2	0.3	0.3	0.3	0.3	0.0	0.0
57.5°	10.8	5.1	0.3	0.3	0.3	0.3	0.3	0.0	0.0
60°	6.3	2.7	0.3	0.3	0.3	0.6	0.3	0.0	0.0
62.5°	3.0	0.9	0.3	0.6	0.6	0.6	0.6	0.3	0.0
65°	1.2	0.3	0.6	0.6	0.6	0.9	0.6	0.3	0.0
67.5°	0.3	0.3	0.6	0.6	0.6	0.9	0.6	0.3	0.3
70°	0.0	0.3	0.6	0.6	0.6	0.9	0.6	0.3	0.3
72.5°	0.0	0.3	0.6	0.6	0.6	0.9	0.6	0.3	0.3
75°	0.0	0.3	0.6	0.6	0.6	0.6	0.6	0.3	0.0
77.5°	0.0	0.3	0.6	0.6	0.6	0.6	0.6	0.3	0.0
80°	0.0	0.3	0.6	0.6	0.6	0.6	0.6	0.3	0.0



TEST NUMBER: P492877

CATALOG NUMBER: LDA2B059027R20D010 2LBDC1MB-30DEG TILT

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
82.5°	0.0	0.3	0.6	0.6	0.6	0.6	0.6	0.3	0.0
85°	0.0	0.3	0.6	0.6	0.6	0.6	0.6	0.3	0.0
87.5°	0.0	0.3	0.6	0.6	0.6	0.6	0.3	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)