

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280255

Luminaire Tested: **LDA2B059040D010 EU2B05WFL559040 2LBALD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059040D010 EU2B05WFL559040 2LBALD1WH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 720.9 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280255

CATALOG NUMBER: LDA2B059040D010 EU2B05WFL559040 2LBALD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P280255

CATALOG NUMBER: LDA2B059040D010 EU2B05WFL559040 2LBALD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95						95													
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90						90													
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85						85													
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80						80													
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76						76													
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72						72													
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69						69													
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65						65													
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62						62													
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59						59													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	615666
5°	603111
10°	560839
15°	489671
20°	405424
25°	310070
30°	169709
35°	62818
40°	21768
45°	9768
50°	4605
55°	2322
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280255

CATALOG NUMBER: LDA2B059040D010 EU2B05WFL559040 2LBALD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.2	15.7
10°-20°	265.0	36.8
20°-30°	250.5	34.7
30°-40°	77.1	10.7
40°-50°	12.2	1.7
50°-60°	2.6	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.6	87.2
0°-40°	705.7	97.9
0°-60°	720.5	99.9
0°-90°	720.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1248	
5°	1218	113
15°	959	265
25°	570	250
35°	104	77
45°	14	12
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280255

CATALOG NUMBER: LDA2B059040D010 EU2B05WFL559040 2LBALD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1247.9
1°	1243.2
2°	1237.5
3°	1232.9
4°	1226.8
5°	1217.8
6°	1206.1
7°	1190.4
8°	1169.3
9°	1144.9
10°	1119.5
11°	1091.5
12°	1061.7
13°	1029.3
14°	995.5
15°	958.7
17.5°	861.5
20°	772.2
22.5°	681.6
25°	569.6
27.5°	434.6
30°	297.9
32.5°	182.9
35°	104.3
37.5°	58.2
40°	33.8
42.5°	21.1
45°	14.0
47.5°	9.4
50°	6.0
52.5°	4.0
55°	2.7
57.5°	1.7
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280255

CATALOG NUMBER: LDA2B059040D010 EU2B05WFL559040 2LBALD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)