

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493238

Luminaire Tested: **LDA2B059030R60D010 2LBDL1WHH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P493238  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059030R60D010 2LBDL1WHH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 571.0 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P493238

CATALOG NUMBER: LDA2B059030R60D010 2LBDL1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P493238

CATALOG NUMBER: LDA2B059030R60D010 2LBDL1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	337953
5°	329141
10°	320071
15°	304212
20°	277948
25°	238704
30°	177628
35°	104255
40°	49720
45°	23164
50°	11590
55°	4043
60°	888
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P493238

CATALOG NUMBER: LDA2B059030R60D010 2LBDL1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.5	11.0
10°-20°	165.7	29.0
20°-30°	196.8	34.5
30°-40°	111.1	19.4
40°-50°	28.9	5.1
50°-60°	5.3	0.9
60°-70°	0.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.1	74.4
0°-40°	536.1	93.9
0°-60°	570.3	99.9
0°-90°	571.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	571.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	685	
5°	665	63
15°	596	166
25°	438	197
35°	173	111
45°	33	29
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493238

CATALOG NUMBER: LDA2B059030R60D010 2LBDL1WHH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	685.0
1°	685.3
2°	680.6
3°	676.6
4°	668.7
5°	664.6
6°	657.4
7°	652.1
8°	647.1
9°	643.6
10°	638.9
11°	629.8
12°	621.3
13°	616.6
14°	605.7
15°	595.6
16°	584.0
17°	570.2
18°	557.1
19°	541.4
20°	529.4
21°	513.1
22.5°	486.2
23°	481.5
24°	458.6
25°	438.5
26°	416.2
27°	390.5
28°	365.1
29°	340.3
30°	311.8
32.5°	239.9
35°	173.1
37.5°	118.2
40°	77.2
42.5°	50.5
45°	33.2
47.5°	22.6
50°	15.1
52.5°	9.4
55°	4.7
57.5°	1.9
60°	0.9
62.5°	0.6
65°	0.6



TEST NUMBER: P493238

CATALOG NUMBER: LDA2B059030R60D010 2LBDL1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)