

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493240

Luminaire Tested: **LDA2B059030R60D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P493240  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059030R60D010 2LBDLC1MB  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 619.0 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P493240

CATALOG NUMBER: LDA2B059030R60D010 2LBDLC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P493240

CATALOG NUMBER: LDA2B059030R60D010 2LBDLC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57		65	60	57		64	60	57	55
10	73	64	58	54	72	63	58	54	62	57	54		61	57	54		61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	366370
5°	356825
10°	346974
15°	329801
20°	301364
25°	258791
30°	192554
35°	113049
40°	53842
45°	25118
50°	12511
55°	4387
60°	987
65°	817
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P493240

CATALOG NUMBER: LDA2B059030R60D010 2LBDLC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.8	11.0
10°-20°	179.7	29.0
20°-30°	213.3	34.5
30°-40°	120.4	19.5
40°-50°	31.3	5.1
50°-60°	5.7	0.9
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	460.8	74.4
0°-40°	581.2	93.9
0°-60°	618.2	99.9
0°-90°	619.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	619.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	743	
5°	720	68
15°	646	180
25°	475	213
35°	188	120
45°	36	31
55°	5	6
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493240

CATALOG NUMBER: LDA2B059030R60D010 2LBDLC1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	742.6
1°	743.0
2°	737.9
3°	733.4
4°	724.9
5°	720.5
6°	712.7
7°	706.9
8°	701.5
9°	697.7
10°	692.6
11°	682.8
12°	673.6
13°	668.5
14°	656.6
15°	645.7
16°	633.1
17°	618.2
18°	603.9
19°	586.9
20°	574.0
21°	556.3
22.5°	527.0
23°	521.9
24°	497.1
25°	475.4
26°	451.2
27°	423.3
28°	395.8
29°	368.9
30°	338.0
32.5°	260.1
35°	187.7
37.5°	128.2
40°	83.6
42.5°	54.7
45°	36.0
47.5°	24.5
50°	16.3
52.5°	10.2
55°	5.1
57.5°	2.0
60°	1.0
62.5°	0.7
65°	0.7



TEST NUMBER: P493240

CATALOG NUMBER: LDA2B059030R60D010 2LBDLC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)