

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493493

Luminaire Tested: **LDA2B059035R70D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P493493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059035R70D010 2LBDL1GPH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 591.2 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P493493

CATALOG NUMBER: LDA2B059035R70D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P493493

CATALOG NUMBER: LDA2B059035R70D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	234051
5°	232716
10°	231149
15°	226882
20°	218673
25°	209363
30°	199390
35°	164544
40°	106975
45°	55887
50°	26019
55°	9548
60°	987
65°	817
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P493493

CATALOG NUMBER: LDA2B059035R70D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	7.5
10°-20°	124.8	21.1
20°-30°	177.2	30.0
30°-40°	165.6	28.0
40°-50°	66.6	11.3
50°-60°	11.7	2.0
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.4	58.6
0°-40°	512.1	86.6
0°-60°	590.4	99.9
0°-90°	591.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	591.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	474	
5°	470	44
15°	444	125
25°	385	177
35°	273	166
45°	80	67
55°	11	12
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493493

CATALOG NUMBER: LDA2B059035R70D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	474.4
1°	475.1
2°	474.1
3°	472.2
4°	471.2
5°	469.9
6°	464.7
7°	466.3
8°	461.7
9°	460.8
10°	461.4
11°	457.2
12°	456.2
13°	451.0
14°	449.0
15°	444.2
16°	441.2
17°	435.4
18°	428.5
19°	424.6
20°	416.5
21°	410.3
22.5°	398.9
23°	396.0
24°	390.4
25°	384.6
26°	380.0
27°	373.5
28°	367.0
29°	359.2
30°	350.0
32.5°	318.1
35°	273.2
37.5°	220.1
40°	166.1
42.5°	118.5
45°	80.1
47.5°	52.8
50°	33.9
52.5°	21.2
55°	11.1
57.5°	3.6
60°	1.0
62.5°	0.7
65°	0.7



TEST NUMBER: P493493

CATALOG NUMBER: LDA2B059035R70D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)