

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279328

Luminaire Tested: **LDA2B059030D010 EU2B05FL409030 2LBALD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059030D010 EU2B05FL409030 2LBALD1WHH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 686.5 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279328

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P279328

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94	92	90	89
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88	86	83	82
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85	83	80	79
7	94	87	82	79	92	86	82	79	85	81	78		84	81	78		83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73		79	75	73		78	75	73	72
10	85	78	74	71	84	78	74	71	77	73	71		76	73	70		76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	944048
5°	924080
10°	842235
15°	657968
20°	389516
25°	144801
30°	45233
35°	20116
40°	9339
45°	4396
50°	2456
55°	1376
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279328

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.5	25.1
10°-20°	343.0	50.0
20°-30°	140.5	20.5
30°-40°	23.2	3.4
40°-50°	5.5	0.8
50°-60°	1.5	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.9	95.5
0°-40°	679.2	98.9
0°-60°	686.2	99.9
0°-90°	686.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1914	
5°	1866	172
15°	1288	343
25°	266	140
35°	33	23
45°	6	6
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279328

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1913.5
1°	1906.9
2°	1898.0
3°	1890.2
4°	1879.8
5°	1865.9
6°	1845.4
7°	1818.6
8°	1780.5
9°	1734.1
10°	1681.2
11°	1619.7
12°	1550.4
13°	1471.3
14°	1383.3
15°	1288.2
17.5°	1021.5
20°	741.9
22.5°	475.0
25°	266.0
27.5°	140.3
30°	79.4
32.5°	50.4
35°	33.4
37.5°	22.1
40°	14.5
42.5°	9.5
45°	6.3
47.5°	4.4
50°	3.2
52.5°	2.2
55°	1.6
57.5°	0.9
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279328

CATALOG NUMBER: LDA2B059030D010 EU2B05FL409030 2LBALD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)