

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280225

Luminaire Tested: **LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 672.3 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280225

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P280225

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	60			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	574224
5°	562501
10°	523116
15°	456727
20°	378123
25°	289221
30°	158259
35°	58602
40°	20287
45°	9140
50°	4298
55°	2150
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P280225

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.5	15.7
10°-20°	247.1	36.8
20°-30°	233.6	34.7
30°-40°	71.9	10.7
40°-50°	11.3	1.7
50°-60°	2.4	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.3	87.2
0°-40°	658.2	97.9
0°-60°	671.9	99.9
0°-90°	672.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	672.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1164	
5°	1136	106
15°	894	247
25°	531	234
35°	97	72
45°	13	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280225

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1163.9
1°	1159.5
2°	1154.2
3°	1149.8
4°	1144.2
5°	1135.8
6°	1124.9
7°	1110.3
8°	1090.6
9°	1067.8
10°	1044.2
11°	1018.0
12°	990.2
13°	960.0
14°	928.5
15°	894.2
17.5°	803.5
20°	720.2
22.5°	635.7
25°	531.3
27.5°	405.3
30°	277.8
32.5°	170.5
35°	97.3
37.5°	54.2
40°	31.5
42.5°	19.6
45°	13.1
47.5°	8.7
50°	5.6
52.5°	3.7
55°	2.5
57.5°	1.6
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280225

CATALOG NUMBER: LDA2B059030D010 EU2B05WFL559030 2LBALD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)