

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P283868

Luminaire Tested: **LDA2B059730D010 EU2B05WFL559730 2LBAPINSQ1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P283868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-61)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059730D010 EU2B05WFL559730 2LBAPINSQ1MW
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in Adj SQ PinHole, MW

Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 543.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.68
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P283868

CATALOG NUMBER: LDA2B059730D010 EU2B05WFL559730 2LBAPINSQ1MW

Luminous Intensity Polar Plot





TEST NUMBER: P283868

CATALOG NUMBER: LDA2B059730D010 EU2B05WFL559730 2LBAPINSQ1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94					94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89					89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	87	90	87	85	84					84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	81	86	83	81	79					79			
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75					75			
6	91	83	78	74	90	82	77	74	81	77	73	80	76	73	78	75	72	71					71			
7	87	79	74	70	86	78	73	70	77	73	69	76	72	69	75	71	69	67					67			
8	84	75	70	66	83	75	70	66	74	69	66	73	69	66	72	68	65	64					64			
9	81	72	67	63	80	71	66	63	71	66	63	70	66	63	69	65	62	61					61			
10	77	69	64	60	76	68	63	60	68	63	60	67	63	60	66	62	60	58					58			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	493954	493954	493954
5°	479101	480240	478061
10°	438551	436798	434143
15°	368875	372297	368262
20°	282096	289551	281623
25°	179150	201959	182634
30°	104195	117640	106018
35°	55049	58602	55229
40°	29046	30399	29046
45°	16257	16885	16466
50°	7599	9594	7599
55°	2752	5247	3011
60°	3158	3158	3158
65°	3385	3736	3385
70°	4183	3750	4183
75°	3812	3812	3812
80°	4262	3409	4262
85°	3396	3396	3396



TEST NUMBER: P283868

CATALOG NUMBER: LDA2B059730D010 EU2B05WFL559730 2LBAPINSQ1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.4	16.5
10°-20°	199.0	36.6
20°-30°	160.7	29.6
30°-40°	63.5	11.7
40°-50°	19.5	3.6
50°-60°	5.0	0.9
60°-70°	3.0	0.6
70°-80°	2.2	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.1	82.7
0°-40°	512.6	94.4
0°-60°	537.1	98.9
0°-90°	543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	543.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	967	969	970	968	965	90
15°	722	724	729	726	721	198
25°	329	345	371	351	336	153
35°	91	94	97	94	92	61
45°	23	24	24	24	24	19
55°	3	4	6	4	4	4
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P283868

CATALOG NUMBER: LDA2B059730D010 EU2B05WFL559730 2LBAPINSQ1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1001.2	1001.2	1001.2	1001.2	1001.2
2.5°	988.6	989.2	990.1	988.9	986.0
5°	967.4	969.1	969.7	967.7	965.3
7.5°	932.4	930.4	932.1	928.7	925.7
10°	875.4	872.7	871.9	866.6	866.6
12.5°	804.9	804.0	804.6	802.0	797.9
15°	722.2	724.2	728.9	726.0	721.0
17.5°	634.5	637.4	641.5	640.7	634.0
20°	537.3	545.7	551.5	546.0	536.4
22.5°	426.6	444.7	459.5	447.9	432.1
25°	329.1	344.8	371.0	351.2	335.5
27.5°	249.6	260.9	284.8	265.3	254.5
30°	182.9	189.9	206.5	193.7	186.1
32.5°	130.8	135.7	142.7	135.1	131.3
35°	91.4	94.1	97.3	94.4	91.7
37.5°	64.4	65.2	67.6	65.2	64.1
40°	45.1	45.4	47.2	45.7	45.1
42.5°	32.6	32.6	33.5	32.9	32.6
45°	23.3	23.6	24.2	23.9	23.6
47.5°	16.6	17.2	17.2	17.5	16.3
50°	9.9	12.2	12.5	12.2	9.9
52.5°	5.2	7.3	9.0	7.3	5.2
55°	3.2	4.4	6.1	4.4	3.5
57.5°	3.2	3.2	4.1	3.5	3.2
60°	3.2	3.2	3.2	3.2	3.2
62.5°	3.2	3.2	3.2	3.2	3.2
65°	2.9	3.2	3.2	3.2	2.9
67.5°	2.9	2.9	2.9	2.9	2.9
70°	2.9	2.9	2.6	2.9	2.9
72.5°	2.6	2.6	2.3	2.6	2.6
75°	2.0	2.0	2.0	2.0	2.0
77.5°	1.7	1.7	1.7	1.7	1.7
80°	1.5	1.5	1.2	1.5	1.5
82.5°	0.9	0.9	0.9	0.9	0.9
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.3	0.3	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)