

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493892

Luminaire Tested: **LDA2B059050R65D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P493892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059050R65D010 2LBD1GPH
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 691.8 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P493892

CATALOG NUMBER: LDA2B059050R65D010 2LBD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P493892

CATALOG NUMBER: LDA2B059050R65D010 2LBD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	81
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72		79	75	72		77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67		74	70	66		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	65	62		69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54		62	58	54		61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	375892
5°	345682
10°	330341
15°	317237
20°	292176
25°	270604
30°	247984
35°	182131
40°	86237
45°	28397
50°	9210
55°	1204
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P493892

CATALOG NUMBER: LDA2B059050R65D010 2LBD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	9.5
10°-20°	172.7	25.0
20°-30°	229.1	33.1
30°-40°	181.3	26.2
40°-50°	39.6	5.7
50°-60°	2.9	0.4
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.4	67.6
0°-40°	648.7	93.8
0°-60°	691.3	99.9
0°-90°	691.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	762	
5°	698	66
15°	621	173
25°	497	229
35°	302	181
45°	41	40
55°	1	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493892

CATALOG NUMBER: LDA2B059050R65D010 2LBD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	761.9
1°	757.8
2°	743.8
3°	728.4
4°	712.3
5°	698.0
6°	688.8
7°	679.5
8°	673.4
9°	664.2
10°	659.4
11°	651.9
12°	643.3
13°	635.8
14°	627.3
15°	621.1
16°	605.4
17°	597.5
18°	584.6
19°	572.6
20°	556.5
21°	543.6
22.5°	526.5
23°	521.7
24°	508.7
25°	497.1
26°	489.9
27°	478.0
28°	466.3
29°	452.3
30°	435.3
32.5°	375.8
35°	302.4
37.5°	215.6
40°	133.9
42.5°	75.5
45°	40.7
47.5°	21.9
50°	12.0
52.5°	5.1
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3



TEST NUMBER: P493892

CATALOG NUMBER: LDA2B059050R65D010 2LBD1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)