

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742573

Luminaire Tested: LD4D10D010-EU4DR600210IC9024-4LBS1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742573  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D10D010-EU4DR600210IC9024-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 920.4 lumens  
Efficiency: N/A  
Efficacy: 78.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742573  
CATALOG NUMBER: LD4D10D010-EU4DR600210IC9024-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P742573

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9024-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			94																
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87			87																
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			81																
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75			75																
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			70																
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			65																
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			61																
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57			57																
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			53																
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			50																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100629
5°	100388
10°	103724
15°	103828
20°	95530
25°	81255
30°	61921
35°	43776
40°	25716
45°	10368
50°	3468
55°	1676
60°	699
65°	103
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10368 cd/sqm



TEST NUMBER: P742573

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9024-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.3	9.6
10°-20°	254.3	27.6
20°-30°	304.4	33.1
30°-40°	203.6	22.1
40°-50°	60.4	6.6
50°-60°	8.7	0.9
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	647.0	70.3
0°-40°	850.5	92.4
0°-60°	919.6	99.9
0°-90°	920.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	920.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	921	
5°	915	88
15°	918	254
25°	674	304
35°	328	204
45°	67	60
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P742573

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9024-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	921.0
2.5°	919.9
5°	915.3
7.5°	927.7
10°	934.9
12.5°	933.6
15°	917.9
17.5°	881.0
20°	821.6
22.5°	750.5
25°	674.0
27.5°	588.0
30°	490.8
32.5°	404.0
35°	328.2
37.5°	252.4
40°	180.3
42.5°	118.9
45°	67.1
47.5°	34.4
50°	20.4
52.5°	13.2
55°	8.8
57.5°	5.6
60°	3.2
62.5°	1.3
65°	0.4
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)