

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P493899

Luminaire Tested: **LDA2B059050R65D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P493899  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-66)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059050R65D010 2LBD1WHH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 90 CRI LEDS AND 5000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 691.8 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.95  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P493899

CATALOG NUMBER: LDA2B059050R65D010 2LBD1WHH

### Luminous Intensity Polar Plot





TEST NUMBER: P493899

CATALOG NUMBER: LDA2B059050R65D010 2LBD1WHH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	67	76	71	67	74	70	66	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56
9	75	65	59	55	73	64	58	54	63	58	54	62	58	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	375892
5°	345682
10°	330341
15°	317237
20°	292176
25°	270604
30°	247984
35°	182131
40°	86237
45°	28397
50°	9210
55°	1204
60°	691
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P493899

CATALOG NUMBER: LDA2B059050R65D010 2LBD1WHH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.6	9.5
10°-20°	172.7	25.0
20°-30°	229.1	33.1
30°-40°	181.3	26.2
40°-50°	39.6	5.7
50°-60°	2.9	0.4
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	467.4	67.6
0°-40°	648.7	93.8
0°-60°	691.3	99.9
0°-90°	691.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	762	
5°	698	66
15°	621	173
25°	497	229
35°	302	181
45°	41	40
55°	1	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P493899

CATALOG NUMBER: LDA2B059050R65D010 2LBD1WHH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	761.9
1°	757.8
2°	743.8
3°	728.4
4°	712.3
5°	698.0
6°	688.8
7°	679.5
8°	673.4
9°	664.2
10°	659.4
11°	651.9
12°	643.3
13°	635.8
14°	627.3
15°	621.1
16°	605.4
17°	597.5
18°	584.6
19°	572.6
20°	556.5
21°	543.6
22.5°	526.5
23°	521.7
24°	508.7
25°	497.1
26°	489.9
27°	478.0
28°	466.3
29°	452.3
30°	435.3
32.5°	375.8
35°	302.4
37.5°	215.6
40°	133.9
42.5°	75.5
45°	40.7
47.5°	21.9
50°	12.0
52.5°	5.1
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3



TEST NUMBER: P493899

CATALOG NUMBER: LDA2B059050R65D010 2LBD1WHH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)