

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279385

Luminaire Tested: **LDA2B059727D010 EU2B05FL409727 2LBAD1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059727D010 EU2B05FL409727 2LBAD1GPH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl, Self-Flanged, GPH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 587.5 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279385

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P279385

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																												
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	807781
5°	790710
10°	720699
15°	562966
20°	333338
25°	123897
30°	38739
35°	17225
40°	7986
45°	3768
50°	2072
55°	1118
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P279385

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	25.1
10°-20°	293.5	50.0
20°-30°	120.2	20.5
30°-40°	19.9	3.4
40°-50°	4.7	0.8
50°-60°	1.2	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.3	95.5
0°-40°	581.2	98.9
0°-60°	587.1	99.9
0°-90°	587.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1637	
5°	1597	148
15°	1102	293
25°	228	120
35°	29	20
45°	5	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279385

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1637.3
1°	1631.7
2°	1624.1
3°	1617.4
4°	1608.5
5°	1596.6
6°	1579.1
7°	1556.1
8°	1523.5
9°	1483.9
10°	1438.6
11°	1386.0
12°	1326.6
13°	1258.9
14°	1183.7
15°	1102.2
17.5°	874.1
20°	634.9
22.5°	406.4
25°	227.6
27.5°	120.0
30°	68.0
32.5°	43.2
35°	28.6
37.5°	18.9
40°	12.4
42.5°	8.1
45°	5.4
47.5°	3.8
50°	2.7
52.5°	1.9
55°	1.3
57.5°	0.8
60°	0.5
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279385

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)