

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278492

Luminaire Tested: **LDA2B059727D010 EU2B05NFL259727 2LBALD1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059727D010 EU2B05NFL259727 2LBALD1MW
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, MW
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 541.3 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278492

CATALOG NUMBER: LDA2B059727D010 EU2B05NFL259727 2LBALD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P278492

CATALOG NUMBER: LDA2B059727D010 EU2B05NFL259727 2LBALD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1385360
5°	1277637
10°	860972
15°	424497
20°	181291
25°	71257
30°	28085
35°	12287
40°	5925
45°	2861
50°	1535
55°	860
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P278492

CATALOG NUMBER: LDA2B059727D010 EU2B05NFL259727 2LBALD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.5	40.4
10°-20°	235.4	43.5
20°-30°	68.0	12.6
30°-40°	14.3	2.6
40°-50°	3.5	0.7
50°-60°	1.0	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.8	96.4
0°-40°	536.2	99.1
0°-60°	540.7	99.9
0°-90°	541.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	541.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2808	
5°	2580	219
15°	831	235
25°	131	68
35°	20	14
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278492

CATALOG NUMBER: LDA2B059727D010 EU2B05NFL259727 2LBALD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2808.0
1°	2790.4
2°	2760.5
3°	2720.2
4°	2663.0
5°	2579.8
6°	2467.5
7°	2321.0
8°	2140.8
9°	1930.7
10°	1718.6
11°	1504.2
12°	1301.8
13°	1122.1
14°	964.1
15°	831.1
17.5°	549.3
20°	345.3
22.5°	212.4
25°	130.9
27.5°	79.9
30°	49.3
32.5°	31.1
35°	20.4
37.5°	13.5
40°	9.2
42.5°	6.4
45°	4.1
47.5°	2.6
50°	2.0
52.5°	1.5
55°	1.0
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P278492

CATALOG NUMBER: LDA2B059727D010 EU2B05NFL259727 2LBALD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)