

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P277951

Luminaire Tested: **LDA2B059727D010 EU2B05SP159727 2LBAD1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P277951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059727D010 EU2B05SP159727 2LBAD1WH
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH SPOT OPTIC AND 2in
ADJ spun Refl, Self-Flanged, WH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 554.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P277951

CATALOG NUMBER: LDA2B059727D010 EU2B05SP159727 2LBAD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P277951

CATALOG NUMBER: LDA2B059727D010 EU2B05SP159727 2LBAD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	99	98	98	98
2	112	109	107	104	110	108	105	103	105	103	101	102	100	99	99	98	97	99	98	97	96
3	109	105	102	100	108	104	101	99	102	99	98	100	98	96	97	96	95	97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95	98	95	94	96	94	93	96	94	93	92
5	104	99	96	93	103	99	95	93	97	94	92	96	93	91	94	92	91	94	92	91	90
6	102	97	93	91	101	96	93	91	95	92	90	94	91	89	93	91	89	93	91	89	88
7	100	95	91	89	99	94	91	88	93	90	88	92	90	88	91	89	87	91	89	87	86
8	98	93	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	90	87	86	85
9	96	91	87	85	95	90	87	85	90	87	85	89	86	84	88	86	84	88	86	84	83
10	94	89	86	83	94	89	85	83	88	85	83	87	85	83	87	85	83	87	85	83	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2502726
5°	1995298
10°	866282
15°	299309
20°	122698
25°	55416
30°	22275
35°	10359
40°	5668
45°	2093
50°	1228
55°	946
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P277951

CATALOG NUMBER: LDA2B059727D010 EU2B05SP159727 2LBAD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.5	55.0
10°-20°	182.9	33.0
20°-30°	50.3	9.1
30°-40°	12.0	2.2
40°-50°	2.9	0.5
50°-60°	1.0	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.7	97.1
0°-40°	549.6	99.2
0°-60°	553.6	99.9
0°-90°	554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5073	
5°	4029	304
15°	586	183
25°	102	50
35°	17	12
45°	3	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P277951

CATALOG NUMBER: LDA2B059727D010 EU2B05SP159727 2LBAD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5072.8
1°	5016.7
2°	4882.3
3°	4677.3
4°	4388.0
5°	4028.9
6°	3590.5
7°	3110.2
8°	2605.5
9°	2141.3
10°	1729.2
11°	1380.2
12°	1098.6
13°	885.9
14°	716.8
15°	586.0
17.5°	363.7
20°	233.7
22.5°	153.3
25°	101.8
27.5°	65.4
30°	39.1
32.5°	24.6
35°	17.2
37.5°	12.6
40°	8.8
42.5°	5.2
45°	3.0
47.5°	2.2
50°	1.6
52.5°	1.4
55°	1.1
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P277951

CATALOG NUMBER: LDA2B059727D010 EU2B05SP159727 2LBAD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)