

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741906

Luminaire Tested: LD4D10D010-EU4DR150210IC9035-4LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P741906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR150210IC9035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1065.5 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741906
CATALOG NUMBER: LD4D10D010-EU4DR150210IC9035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P741906

CATALOG NUMBER: LD4D10D010-EU4DR150210IC9035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1633475	1633475	1633475
5°	959905	947476	954976
10°	286492	288498	292911
15°	71257	72647	70406
20°	21323	24694	21773
25°	7517	9574	7611
30°	2763	3639	2808
35°	1387	1561	1336
40°	873	959	873
45°	644	686	644
50°	515	515	515
55°	425	425	425
60°	344	344	344
65°	264	264	264
70°	227	227	227
75°	136	136	189
80°	95	95	95
85°	50	50	50

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 686 cd/sqm



TEST NUMBER: P741906

CATALOG NUMBER: LD4D10D010-EU4DR150210IC9035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	691.0	64.9
10°-20°	284.2	26.7
20°-30°	56.5	5.3
30°-40°	14.1	1.3
40°-50°	7.4	0.7
50°-60°	5.5	0.5
60°-70°	3.9	0.4
70°-80°	2.2	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.8	96.8
0°-40°	1045.9	98.2
0°-60°	1058.7	99.4
0°-90°	1065.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1065.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14517	14517	14517	14517	14517	
5°	9445	9348	9323	9387	9397	690
15°	820	836	836	822	811	281
25°	96	109	123	109	98	51
35°	19	20	22	20	18	13
45°	9	9	10	9	9	7
55°	6	6	6	6	6	5
65°	4	4	4	4	4	4
75°	2	2	2	2	2	2
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P741906

CATALOG NUMBER: LD4D10D010-EU4DR150210IC9035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14517.2	14517.2	14517.2	14517.2	14517.2
2.5°	13095.1	13106.2	13110.5	13123.4	13171.3
5°	9445.2	9348.1	9322.9	9387.4	9396.7
7.5°	5595.0	5614.6	5686.6	5702.5	5644.8
10°	3070.4	3095.6	3091.9	3114.0	3139.2
12.5°	1570.2	1550.5	1544.4	1569.6	1534.6
15°	820.4	835.8	836.4	821.7	810.6
17.5°	441.3	459.1	488.6	464.6	427.7
20°	260.6	276.6	301.8	282.1	266.1
22.5°	161.0	173.9	191.7	176.4	163.5
25°	96.5	109.4	122.9	108.8	97.7
27.5°	57.2	68.2	76.8	67.6	56.5
30°	36.9	43.0	48.6	42.4	37.5
32.5°	25.8	28.3	30.7	28.3	25.8
35°	19.1	20.3	21.5	20.3	18.4
37.5°	14.7	16.0	16.6	15.4	14.1
40°	12.3	12.9	13.5	12.9	12.3
42.5°	10.4	11.1	11.1	11.1	10.4
45°	9.2	9.2	9.8	9.2	9.2
47.5°	8.0	8.0	8.6	8.0	8.0
50°	7.4	7.4	7.4	7.4	7.4
52.5°	6.8	6.8	6.8	6.8	6.8
55°	6.1	6.1	6.1	6.1	6.1
57.5°	5.5	5.5	5.5	5.5	5.5
60°	4.9	4.9	4.9	4.9	4.9
62.5°	4.3	4.3	4.3	4.3	4.3
65°	3.7	3.7	3.7	3.7	3.7
67.5°	3.7	3.7	3.7	3.7	3.7
70°	3.1	3.1	3.1	3.1	3.1
72.5°	2.5	2.5	2.5	2.5	2.5
75°	1.8	1.8	1.8	1.8	2.5
77.5°	1.8	1.8	1.8	1.8	1.8
80°	1.2	1.2	1.2	1.2	1.2
82.5°	1.2	1.2	1.2	1.2	1.2
85°	0.6	0.6	0.6	0.6	0.6
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)