

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742145

Luminaire Tested: LD4D10D010-EU4DR300210IC9035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P742145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR300210IC9035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1138.7 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742145
CATALOG NUMBER: LD4D10D010-EU4DR300210IC9035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P742145

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	280256	280256	280256
5°	272214	271899	272229
10°	235776	234113	235722
15°	153836	153003	152243
20°	76495	79362	76389
25°	38529	43453	37744
30°	15432	16811	13443
35°	7158	6849	5747
40°	3088	3427	2908
45°	2176	2706	2197
50°	750	1977	786
55°	427	814	454
60°	306	352	306
65°	199	199	199
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2706 cd/sqm



TEST NUMBER: P742145

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.0	28.3
10°-20°	518.5	45.5
20°-30°	224.1	19.7
30°-40°	51.1	4.5
40°-50°	17.5	1.5
50°-60°	4.3	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1064.6	93.5
0°-40°	1115.6	98.0
0°-60°	1137.4	99.9
0°-90°	1138.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1138.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3661	3661	3661	3661	3661	
5°	3543	3539	3539	3546	3543	322
15°	1941	1918	1931	1924	1921	520
25°	456	474	514	462	447	218
35°	77	78	73	73	62	52
45°	20	25	25	25	20	14
55°	3	3	6	4	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P742145

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3661.4	3661.4	3661.4	3661.4	3661.4
2.5°	3637.1	3634.6	3636.1	3637.9	3638.6
5°	3542.8	3539.4	3538.7	3546.0	3543.0
7.5°	3352.4	3347.6	3340.2	3356.9	3372.6
10°	3033.5	3028.1	3012.1	3020.0	3032.8
12.5°	2562.7	2545.3	2544.9	2570.1	2566.6
15°	1941.3	1917.9	1930.8	1924.5	1921.2
17.5°	1305.5	1296.5	1313.7	1308.5	1286.0
20°	939.1	941.4	974.3	957.8	937.8
22.5°	685.2	693.7	732.7	690.1	674.5
25°	456.2	473.5	514.5	461.5	446.9
27.5°	280.6	288.5	330.0	277.0	269.1
30°	174.6	170.6	190.2	163.2	152.1
32.5°	114.5	109.5	115.8	103.9	94.9
35°	76.6	78.2	73.3	72.8	61.5
37.5°	47.8	55.0	48.5	51.8	39.5
40°	30.9	39.9	34.3	37.9	29.1
42.5°	25.3	30.8	28.2	30.0	25.9
45°	20.1	25.0	25.0	25.0	20.3
47.5°	11.2	16.7	21.4	17.1	11.9
50°	6.3	8.4	16.6	8.8	6.6
52.5°	4.3	4.9	11.3	5.0	4.5
55°	3.2	3.4	6.1	3.6	3.4
57.5°	2.5	2.7	3.2	2.7	2.5
60°	2.0	2.0	2.3	2.2	2.0
62.5°	1.4	1.4	1.6	1.4	1.4
65°	1.1	1.1	1.1	1.1	1.1
67.5°	0.5	0.7	0.7	0.7	0.7
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)