

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494085

Luminaire Tested: **LDA2B059727R60D010 2LBD1GPH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494085  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059727R60D010 2LBD1GPH  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 533.9 lumens  
Efficiency: N/A  
Efficacy: 76.3 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494085  
CATALOG NUMBER: LDA2B059727R60D010 2LBD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P494085

CATALOG NUMBER: LDA2B059727R60D010 2LBD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65		73	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	319649
5°	303437
10°	297077
15°	287510
20°	262880
25°	233423
30°	174608
35°	98594
40°	37097
45°	16606
50°	8059
55°	1634
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P494085

CATALOG NUMBER: LDA2B059727R60D010 2LBD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.0	10.9
10°-20°	156.3	29.3
20°-30°	191.0	35.8
30°-40°	104.2	19.5
40°-50°	20.8	3.9
50°-60°	3.0	0.6
60°-70°	0.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.4	75.9
0°-40°	509.6	95.4
0°-60°	533.4	99.9
0°-90°	533.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	648	
5°	613	58
15°	563	156
25°	429	191
35°	164	104
45°	24	21
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494085

CATALOG NUMBER: LDA2B059727R60D010 2LBD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	647.9
1°	644.9
2°	639.2
3°	631.6
4°	620.8
5°	612.7
6°	608.4
7°	603.2
8°	599.2
9°	597.3
10°	593.0
11°	588.1
12°	583.8
13°	578.6
14°	571.0
15°	562.9
16°	552.6
17°	538.3
18°	529.1
19°	514.2
20°	500.7
21°	488.3
22.5°	467.4
23°	458.8
24°	445.5
25°	428.8
26°	407.4
27°	384.9
28°	359.2
29°	334.9
30°	306.5
32.5°	235.1
35°	163.7
37.5°	102.5
40°	57.6
42.5°	36.0
45°	23.8
47.5°	16.2
50°	10.5
52.5°	5.4
55°	1.9
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3



TEST NUMBER: P494085

CATALOG NUMBER: LDA2B059727R60D010 2LBD1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)