

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494122

Luminaire Tested: **LDA2B059727R65D010 2LBDL1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-68)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B059727R65D010 2LBDL1MMS
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 2700K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 506.3 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.94
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494122

CATALOG NUMBER: LDA2B059727R65D010 2LBDL1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P494122

CATALOG NUMBER: LDA2B059727R65D010 2LBDL1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74
5	92	83	77	73	90	82	76	72	80	75	72	79	74	71	77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60
8	78	68	62	58	77	68	62	58	67	61	58	66	61	57	65	60	57	56
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	53	52
10	71	61	55	51	70	60	54	51	59	54	50	59	54	50	58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264935
5°	253863
10°	241769
15°	229793
20°	213738
25°	197332
30°	171190
35°	122866
40°	66722
45°	28467
50°	12281
55°	4387
60°	789
65°	584
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P494122

CATALOG NUMBER: LDA2B059727R65D010 2LBDL1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.0	9.5
10°-20°	126.0	24.9
20°-30°	164.8	32.5
30°-40°	125.3	24.8
40°-50°	36.2	7.2
50°-60°	5.5	1.1
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.8	66.9
0°-40°	464.1	91.7
0°-60°	505.8	99.9
0°-90°	506.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	506.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	537	
5°	513	48
15°	450	126
25°	362	165
35°	204	125
45°	41	36
55°	5	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494122

CATALOG NUMBER: LDA2B059727R65D010 2LBDL1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	537.0
1°	535.1
2°	532.1
3°	526.1
4°	519.6
5°	512.6
6°	505.8
7°	499.9
8°	494.2
9°	489.1
10°	482.6
11°	476.9
12°	471.0
13°	465.0
14°	458.5
15°	449.9
16°	443.4
17°	435.5
18°	423.6
19°	417.4
20°	407.1
21°	397.9
22.5°	383.8
23°	378.4
24°	370.1
25°	362.5
26°	352.5
27°	341.4
28°	329.2
29°	316.2
30°	300.5
32.5°	257.5
35°	204.0
37.5°	150.4
40°	103.6
42.5°	65.7
45°	40.8
47.5°	25.4
50°	16.0
52.5°	9.5
55°	5.1
57.5°	1.9
60°	0.8
62.5°	0.5
65°	0.5



TEST NUMBER: P494122

CATALOG NUMBER: LDA2B059727R65D010 2LBDL1MMS

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)