

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742609

Luminaire Tested: LD4D10D010-EU4DR600210IC9035-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742609  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D10D010-EU4DR600210IC9035-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1110.9 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742609  
CATALOG NUMBER: LD4D10D010-EU4DR600210IC9035-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P742609

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9035-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144148
5°	147693
10°	149478
15°	142401
20°	125551
25°	101556
30°	68696
35°	34426
40°	5577
45°	5470
50°	5575
55°	5658
60°	5813
65°	5946
70°	6102
75°	6163
80°	5977
85°	5015

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 6163 cd/sqm



TEST NUMBER: P742609

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9035-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.7	11.6
10°-20°	348.2	31.3
20°-30°	374.7	33.7
30°-40°	162.9	14.7
40°-50°	27.3	2.5
50°-60°	26.6	2.4
60°-70°	22.7	2.0
70°-80°	15.2	1.4
80°-90°	4.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	851.6	76.7
0°-40°	1014.4	91.3
0°-60°	1068.3	96.2
0°-90°	1110.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1319	
5°	1347	129
15°	1259	348
25°	842	375
35°	258	163
45°	35	27
55°	30	27
65°	23	23
75°	15	15
85°	4	5
90°	0	



TEST NUMBER: P742609

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9035-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1319.3
2.5°	1356.4
5°	1346.6
7.5°	1349.7
10°	1347.3
12.5°	1319.5
15°	1258.9
17.5°	1177.5
20°	1079.8
22.5°	975.2
25°	842.4
27.5°	673.7
30°	544.5
32.5°	419.6
35°	258.1
37.5°	110.4
40°	39.1
42.5°	36.0
45°	35.4
47.5°	34.1
50°	32.8
52.5°	31.2
55°	29.7
57.5°	28.1
60°	26.6
62.5°	24.9
65°	23.0
67.5°	21.1
70°	19.1
72.5°	16.8
75°	14.6
77.5°	12.0
80°	9.5
82.5°	6.7
85°	4.0
87.5°	1.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)