

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742690

Luminaire Tested: LD4D10D010-EU4DR650210IC9035-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742690  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D10D010-EU4DR650210IC9035-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 973.1 lumens  
Efficiency: N/A  
Efficacy: 83.2 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742690  
CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P742690

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	51600
5°	51474
10°	51429
15°	49847
20°	45377
25°	39541
30°	32890
35°	26059
40°	18809
45°	11885
50°	6197
55°	3289
60°	1729
65°	954
70°	393
75°	429
80°	303
85°	268

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11885 cd/sqm



TEST NUMBER: P742690

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.6	8.6
10°-20°	228.8	23.5
20°-30°	279.7	28.7
30°-40°	226.9	23.3
40°-50°	113.1	11.6
50°-60°	31.5	3.2
60°-70°	7.2	0.7
70°-80°	1.8	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.0	60.8
0°-40°	819.0	84.2
0°-60°	963.6	99.0
0°-90°	973.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	973.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	884	
5°	878	84
15°	824	229
25°	614	280
35°	366	227
45°	144	113
55°	32	32
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P742690

CATALOG NUMBER: LD4D10D010-EU4DR650210IC9035-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	883.5
2.5°	882.9
5°	878.0
7.5°	875.1
10°	867.2
12.5°	851.1
15°	824.4
17.5°	782.5
20°	730.1
22.5°	673.4
25°	613.6
27.5°	549.6
30°	487.7
32.5°	426.5
35°	365.5
37.5°	304.6
40°	246.7
42.5°	192.4
45°	143.9
47.5°	100.2
50°	68.2
52.5°	47.0
55°	32.3
57.5°	21.8
60°	14.8
62.5°	10.3
65°	6.9
67.5°	3.5
70°	2.3
72.5°	2.2
75°	1.9
77.5°	1.3
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)