

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742153

Luminaire Tested: LD4D10D010-EU4DR300210IC9040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P742153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR300210IC9040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1058.7 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742153

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P742153

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	260577	260577	260577
5°	253097	252805	253112
10°	219221	217674	219167
15°	143035	142266	141545
20°	71119	73791	71029
25°	35826	40404	35092
30°	14345	15626	12498
35°	6653	6373	5345
40°	2878	3187	2708
45°	2024	2511	2046
50°	691	1834	738
55°	400	761	427
60°	276	337	276
65°	181	181	181
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 2511 cd/sqm



TEST NUMBER: P742153

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.4	28.3
10°-20°	482.1	45.5
20°-30°	208.3	19.7
30°-40°	47.5	4.5
40°-50°	16.3	1.5
50°-60°	4.0	0.4
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.8	93.5
0°-40°	1037.3	98.0
0°-60°	1057.6	99.9
0°-90°	1058.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1058.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3404	3404	3404	3404	3404	
5°	3294	3291	3290	3297	3294	300
15°	1805	1783	1795	1789	1786	483
25°	424	440	478	429	416	203
35°	71	73	68	68	57	48
45°	19	23	23	23	19	13
55°	3	3	6	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P742153

CATALOG NUMBER: LD4D10D010-EU4DR300210IC9040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3404.3	3404.3	3404.3	3404.3	3404.3
2.5°	3381.8	3379.4	3380.8	3382.4	3383.1
5°	3294.0	3290.9	3290.2	3297.0	3294.2
7.5°	3117.0	3112.5	3105.6	3121.2	3135.7
10°	2820.5	2815.5	2800.6	2808.0	2819.8
12.5°	2382.8	2366.6	2366.2	2389.6	2386.5
15°	1805.0	1783.3	1795.3	1789.4	1786.2
17.5°	1213.8	1205.4	1221.5	1216.6	1195.7
20°	873.1	875.3	905.9	890.5	872.0
22.5°	637.1	645.0	681.2	641.6	627.1
25°	424.2	440.3	478.4	429.0	415.5
27.5°	260.9	268.3	306.9	257.5	250.2
30°	162.3	158.6	176.8	151.8	141.4
32.5°	106.5	101.8	107.7	96.6	88.2
35°	71.2	72.7	68.2	67.7	57.2
37.5°	44.5	51.2	45.1	48.1	36.8
40°	28.8	37.1	31.9	35.3	27.1
42.5°	23.5	28.6	26.2	27.9	24.1
45°	18.7	23.2	23.2	23.2	18.9
47.5°	10.4	15.5	19.9	15.9	11.1
50°	5.8	7.8	15.4	8.2	6.2
52.5°	4.0	4.5	10.5	4.7	4.2
55°	3.0	3.2	5.7	3.3	3.2
57.5°	2.3	2.5	3.0	2.5	2.3
60°	1.8	1.8	2.2	2.0	1.8
62.5°	1.3	1.3	1.5	1.3	1.3
65°	1.0	1.0	1.0	1.0	1.0
67.5°	0.5	0.7	0.7	0.7	0.7
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)