

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494277

Luminaire Tested: **LDA2B059730R45D010 2LBD1B**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494277  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059730R45D010 2LBD1B  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 595.1 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494277  
CATALOG NUMBER: LDA2B059730R45D010 2LBD1B

### Luminous Intensity Polar Plot





TEST NUMBER: P494277

CATALOG NUMBER: LDA2B059730R45D010 2LBD1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100		
1	114	112	110	108	112	110	108	106	106	104	103	103	102	101	100	100	99	98	97	97	95	95		
2	110	106	102	99	108	104	101	98	101	98	96	96	98	96	94	94	95	94	92	92	91	91		
3	105	100	96	93	104	99	95	92	96	93	90	90	94	91	89	89	92	90	88	88	86	86		
4	101	95	90	87	100	94	90	86	92	88	85	85	90	87	84	84	88	86	83	83	82	82		
5	97	90	86	82	96	90	85	82	88	84	81	81	86	83	80	80	85	82	80	80	78	78		
6	94	86	81	78	92	86	81	77	84	80	77	77	83	79	76	76	82	78	76	76	75	75		
7	90	82	77	74	89	82	77	74	81	76	73	73	80	76	73	73	78	75	73	73	71	71		
8	87	79	74	70	86	78	74	70	77	73	70	70	76	73	70	70	76	72	70	70	68	68		
9	84	76	71	67	83	75	70	67	74	70	67	67	73	70	67	67	73	69	67	67	66	66		
10	81	73	68	65	80	72	68	64	71	67	64	64	71	67	64	64	70	67	64	64	63	63		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	590603
5°	581568
10°	542754
15°	473633
20°	362162
25°	210342
30°	89213
35°	36920
40°	16294
45°	8442
50°	4221
55°	1032
60°	592
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P494277

CATALOG NUMBER: LDA2B059730R45D010 2LBD1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.3	18.4
10°-20°	252.9	42.5
20°-30°	176.8	29.7
30°-40°	43.8	7.4
40°-50°	10.1	1.7
50°-60°	1.7	0.3
60°-70°	0.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.0	90.6
0°-40°	582.8	97.9
0°-60°	594.6	99.9
0°-90°	595.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1197	
5°	1174	109
15°	927	253
25°	386	177
35°	61	44
45°	12	10
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494277

CATALOG NUMBER: LDA2B059730R45D010 2LBD1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1197.1
1°	1194.5
2°	1193.9
3°	1190.2
4°	1179.5
5°	1174.3
6°	1163.7
7°	1148.4
8°	1129.7
9°	1110.4
10°	1083.4
11°	1061.2
12°	1034.1
13°	999.0
14°	963.3
15°	927.3
16°	887.6
17°	840.4
18°	792.6
19°	743.4
20°	689.8
21°	625.6
22.5°	542.4
23°	508.1
24°	446.5
25°	386.4
26°	329.9
27°	277.2
28°	230.9
29°	190.6
30°	156.6
32.5°	96.4
35°	61.3
37.5°	39.7
40°	25.3
42.5°	17.3
45°	12.1
47.5°	8.6
50°	5.5
52.5°	2.9
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.3
65°	0.3



TEST NUMBER: P494277

CATALOG NUMBER: LDA2B059730R45D010 2LBD1B

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)